EPIC® H-B 48 SDR-LB

Housing design H-B for 2 inserts.

The large housing for the placement of two inserts consists of a single lever, a cable entry and a thermoplastic cap.





Benefits

The large, robust housing for two inserts in one connector. Power and data in a single connector
M40 housing extension on M50 with SKINTOP 53112083 possible (clamping range 27 - 35 mm)

Application range

Plant engineering
Plastics industry

Product features

Surface-mount base
Single lever
1 cable entry
Plastic cover

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Last Update (01.06.2026)
©2026 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® H-B 48 SDR-LB

Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (01.06.2026)
©2026 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® H-B 48 SDR-LB

Article number	Article description	M	Packaging unit
19167000	H-B 48 SDR M32	32	1
19167100	H-B 48 SDR M40	40	1

Last Update (01.06.2026)
©2026 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16