

## EPIC® H-Q Cable coupler plastic

EPIC® H-Q Cable coupler plastic housing for H-Q rectangular connector series



Corrosion-resistant



Low weight



Optimum strain relief

### Benefits

Housing in plastic or metal version. For power supply in the smallest possible space neck for cable gland integrated, use with special H-Q cable glands with metal housing EMC cable gland as an option

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: thermoplastic, grey Lever: metal
Protection rating:	IP 66
Temperature range:	-40°C to +125°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® H-Q Cable coupler plastic**

Article number	Article description	M	Pieces / PU
H-Q housings – cable coupler hoods (straight cable entry)			
44420533	H-Q KG V16P	V16P	1

Last Update (06.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03.16