

EPIC® MH 0.8mm contacts stamped

The mixed assembly guarantees high flexibility. For applications in mechanical and plant engineering, for printing machines and slide-in technology.

EPIC® MH 0.8mm contacts stamped

Info

Modular connector system, plugable with the market standard
Gold-plated contacts for low transfer resistance
Stamped gold plated contacts with 0.8 mm diameter for D-Sub inserts

Benefits

Modular connector system, plugable with the market standard
Gold-plated contacts for low transfer resistance

Application range

Mechanical and plant engineering
Robotics industry
Renewable energy
Railway applications / vehicle construction

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® MH 0.8mm contacts stamped

Article number	Article description	Contact type	Conductor cross-section AWG	Pieces / PU
44423324	EPIC® MH SCEG AU 0.09 - 0.25sqmm D=0.8	male	28.0 - 24.0	100
44423325	EPIC® MH BCEG AU 0.09 - 0.25sqmm D=1.0	female	28.0 - 24.0	100

Last Update (01.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16