

EPIC® MH 1.0mm contacts stamped

The mixed assembly guarantees high flexibility. For applications in mechanical and plant engineering, for printing machines and slide-in technology.

EPIC® MH 1.0mm contacts stamped

Info

Stamped gold plated contacts with 1.0mm diameter for D-Sub inserts



Benefits

Stamped gold plated contacts with 1.0mm diameter for D-Sub inserts
Gold-plated contacts for low transfer resistance

Application range

Mechanical and plant engineering
Robotics industry
Renewable energy
Railway applications / vehicle construction

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000796 ETIM 5.0 Class-Description: Contact for industrial connectors
Termination methods:	Crimp termination
Stripping length (mm):	3 ± 0.5
Material:	brass gold plated CuZn / Au
Cycle of mechanical operation:	500

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® MH 1.0mm contacts stamped

Article number	Article description	Contact type	Conductor cross-section AWG	Pieces / PU
44423320	EPIC® MH SCEG AU 0.09 - 0.25sqmm D=1.0	male	28.0 - 24.0	100
44423322	EPIC® MH BCEG AU 0.09 - 0.25sqmm D=1.0	female	28.0 - 24.0	100
44423321	EPIC® MH SCEG AU 0.25 - 0.52 sqmm D=1.0	male	24.0 - 20.0	100
44423323	EPIC® MH SCEG AU 0.25 - 0.52 sqmm D=1.0	female	24.0 - 20.0	100

Last Update (22.10.2019)

©2019 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16