

EPIC® MH 4.0mm Contacts

High flexibility by the use of any combination of inserts in one connector

Machined EPIC® MH 4.0 contacts are suitable for the safe transmission of larger currents. The silver coating ensures low contact resistance and thus little loss and less heat generation.

Info

High quality contact with 4mm pin diameter for a safe transmission of larger currents



Supplementary automation components from Lapp



Mechanical and plant engineering



Rail



Wind Energy



Robust

Benefits

High quality contact with 4mm pin diameter for a safe transmission of larger currents

For cross section from 1,5mm² up to 10mm² available

Crimp connection for permanent vibration proof contacting

With the appropriate tools, good contacting is created quickly and easily

Application range

Mechanical engineering

Robotics industry

Plant engineering

Renewable energy

Railway applications / vehicle construction

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000796

Last Update (06.06.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® MH 4.0mm Contacts

Classification ETIM 6:	ETIM 5.0 Class-Description: Contact for industrial connectors ETIM 6.0 Class-ID: EC000796 ETIM 6.0 Class-Description: Contact for industrial connectors
Contact resistance:	< 5 mOhm
Termination methods:	Crimp termination: 1.5 - 10 mm ²
Stripping length (mm):	10
Cycle of mechanical operation:	500

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® MH 4.0mm Contacts

Article number	Article description	Contact type	Connection cross section (mm ²)	Pieces / PU
44423250	EPIC® MH SCEM AG 1.5sqmm D=4.0	male	1.5	100
44423255	EPIC® MH BCEM AG 1.5sqmm D=4.0	female	1.5	100
44423251	EPIC® MH SCEM AG 2.5sqmm D=4.0	male	2.5	100
44423256	EPIC® MH BCEM AG 2.5sqmm D=4.0	female	2.5	100
44423252	EPIC® MH SCEM AG 4sqmm D=4.0	male	4	100
44423257	EPIC® MH BCEM AG 4sqmm D=4.0	female	4	100
44423253	EPIC® MH SCEM AG 6sqmm D=4.0	male	6	100
44423258	EPIC® MH BCEM AG 6sqmm D=4.0	female	6	100
44423254	EPIC® MH SCEM AG 10sqmm D=4.0	male	10	100
44423259	EPIC® MH BCEM AG 10sqmm D=4.0	female	10	100

Last Update (06.06.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16