

EPIC® MH 8.0mm Contacts

High flexibility by the use of any combination of inserts in one connector

Info

Modular connector system, plugable with the market standard



Supplementary automation components from Lapp



Mechanical and plant engineering



Rail



Wind Energy



Flame-retardant



Voltage

Benefits

Crimp connection for permanent vibration proof contacting
EPIC® MH system is mateable with the market standard

Application range

Mechanical engineering
Robot-building
Plant engineering
Renewable energy
Railway applications / vehicle construction

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000796

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® MH 8.0mm Contacts

| | |
|--------------------------------|---|
| Classification ETIM 6: | ETIM 5.0 Class-Description: Contact for industrial connectors ETIM 6.0 Class-ID: EC000796 ETIM 6.0 Class-Description: Contact for industrial connectors |
| Contact resistance: | < 5 mOhm |
| Termination methods: | Crimp termination: 10 mm ² ... 35 mm ² |
| Stripping length (mm): | 18 |
| Cycle of mechanical operation: | 500 |

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® MH 8.0mm Contacts

| Article number | Article description | Contact type | Connection cross section (mm ²) | Pieces / PU |
|-------------------------|----------------------------------|--------------|---|-------------|
| EPIC® MH D=8.0 contacts | | | | |
| 44423242 | EPIC® MH SCEM AG 10sqmm D=8.0 | male | 10 | 10 |
| 44423246 | EPIC® MH BCEM AG 10sqmm D=8.0 | female | 10 | 10 |
| 44423243 | EPIC® MH SCEM AG 16sqmm D=8.0 | male | 16 | 10 |
| 44423247 | EPIC® MH BCEM AG 16sqmm D=8.0 | female | 16 | 10 |
| 44423244 | EPIC® MH SCEM AG 25sqmm D=8.0 | male | 25 | 10 |
| 44423248 | EPIC® MH BCEM AG 25sqmm D=8.0 | female | 25 | 10 |
| 44423245 | EPIC® MH SCEM AG 35sqmm D=8.0 | male | 35 | 10 |
| 44423249 | EPIC® MH BCEM AG 35sqmm D=8.0 | female | 35 | 10 |

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16