


FLEXIMARK® Collar closed

FLEXIMARK® Collar halogen free are character holders for marking wires before assembly, halogen free and flame-retardant

Info

Mounting before installation, as marking collar is closed



Flame-retardant



Halogen-free

Benefits

Enhanced scratch-protection

Resistant and flexible protection

Resistant to chemicals, UV-light, moisture and oils (diesel oil, basic cleaning agent, sea water, ethanol,...)

Product features

Extremely flame-retardant according to
UL 94 V0

Note

Suitable marking collar for LMB labels

Included

Marking collars without labels

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002248

ETIM 5.0 Class-Description: Mounting for labelling material

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002248

ETIM 6.0 Class-Description: Mounting for labelling material

Colour delivered:

Transparent

Material:

PVC

Temperature range:

-40°C to +80°C

Last Update (22.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FLEXIMARK® Collar closed

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

FLEXIMARK® Collar closed

Article number	Article designation	Length (mm)	For cable Ø (mm)	Markers / PU	PU
FLEXIMARK® Collar closed					
83290211	FLEXIMARK® collar halogen-free 2-4/10 TR	10	2.0 - 4.0	1000	1
83290212	FLEXIMARK® collar halogen-free 2-4/15 TR	15	2.0 - 4.0	1000	1
83252693	FLEXIMARK® collar halogenfree 1,4-5/23 TR	23	1.4 - 5.0	500	1
83290213	FLEXIMARK® collar halogen-free 2-4/30 TR	30	2.0 - 4.0	500	1
83290214	FLEXIMARK® collar halogen-free 4-7/10 TR	10	4.0 - 7.0	500	1
83290215	FLEXIMARK® collar halogen-free 4-7/15 TR	15	4.0 - 7.0	500	1
83252694	FLEXIMARK® collar halogen-free 5-11/23 TR	23	5.0 - 11.0	200	1
83252675	FLEXIMARK® collar halogen-free 5-11/30 TR	30	5.0 - 11.0	200	1