


FLEXIMARK® Wrapping label LCK

FLEXIMARK® LCK wrapping labels are markers of vinyl with an protective transparent foil for marking cables with a laser printer. The protection foil protects the text from abrasion and solvents.

Info

LCK 32 YE included in FLEXIMARK® sample bag (article no. M3251010)



Food & Beverage



Mechanical and plant engineering



Solar Energy



Wind Energy



Good chemical resistance



Halogen-free



Space requirement



UV-resistant



Waterproof

Benefits

A transparent film is wrapped around the cable and pasted over the printed field so that the printing is protected against abrasion, pollution and solvents

Resistant to chemicals, UV-light, moisture and oils (diesel oil, basic cleaning agent, sea water, ethanol,...)

Due to tight wrapping, space-saving

Last Update (12.02.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FLEXIMARK® Wrapping label LCK

Application range

For cable marking

Note

Can be printed with the FLEXIMARK® Software and a commercial laser printer

Insert sheet in manual paper feed compartment

Optimum printing results from laser printers are achieved with straight sheet feed-in

Included

10 or 100 perforated DIN A4 label sheets (dependent on the chosen packaging size)

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001530 ETIM 5.0 Class-Description: Cable coding system
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001530 ETIM 6.0 Class-Description: Cable coding system
Adhesive:	Acrylic-based permanent adhesive
Colour delivered:	Yellow, white
Material:	Halogen-free polyester Thickness: 0.025 mm
Temperature range:	-40°C to +125°C Minimum working temperature: +10°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

FLEXIMARK® Wrapping label LCK

Article number	Article designation	Colour	Width x length (mm)	Labelling surface (mm)	For outer Ø (mm)	Markers / PU	PU
Small packaging (10 sheets)							
83256142	FLEXIMARK® Label LCK 32 YE	yellow	25.0 x 33.5	25.0 x 12.7	4.0 - 7.0	640	1
83256144	FLEXIMARK® Label LCK 35 YE	yellow	25.0 x 55.0	25.0 x 19.0	6.0 - 12.0	400	1
83256146	FLEXIMARK® Label LCK 40 YE	yellow	25.0 x 94.0	25.0 x 25.4	8.0 - 21.0	240	1
83256148	FLEXIMARK® Label LCK 45 YE	yellow	25.0 x 142.5	25.5 x 25.4	8.0 - 36.0	160	1
83256161	FLEXIMARK® Label LCK 48 YE	yellow	34.0 x 93.0	34.0 x 25.4	8.0 - 21.0	180	1
83256150	FLEXIMARK® Label LCK 60 YE	yellow	50.0 x 56.0	50.0 x 19.0	6.0 - 12.0	200	1
83256152	FLEXIMARK® Label LCK 65 YE	yellow	50.0 x 94.0	50.0 x 25.4	8.0 - 21.0	120	1
83256154	FLEXIMARK® Label LCK 70 YE	yellow	50.0 x 142.5	50.0 x 25.4	8.0 - 36.0	80	1
83256143	FLEXIMARK® Label LCK 32 WH	white	25.0 x 33.5	25.0 x 12.7	4.0 - 7.0	640	1
83256145	FLEXIMARK® Label LCK 35 WH	white	25.0 x 55.0	25.0 x 19.0	6.0 - 12.0	400	1
83256147	FLEXIMARK® Label LCK 40 WH	white	25.0 x 94.0	25.0 x 25.4	8.0 - 21.0	240	1
83256149	FLEXIMARK® Label LCK 45 WH	white	25.0 x 142.5	25.0 x 25.4	8.0 - 36.0	160	1
83256160	FLEXIMARK® Label LCK 48 WH	white	34.0 x 93.0	34.0 x 25.4	8.0 - 21.0	180	1
83256151	FLEXIMARK® Label LCK 60 WH	white	50.0 x 56.0	50.0 x 19.0	6.0 - 12.0	200	1
83256153	FLEXIMARK® Label LCK 65 WH	white	50.0 x 94.0	50.0 x 25.4	8.0 - 21.0	120	1
83256155	FLEXIMARK® Label LCK 70 WH	white	50.0 x 142.5	50.0 x 25.4	8.0 - 36.0	80	1
Large packaging (100 sheets)							
83256542	FLEXIMARK® Label LCK 32 YE-100	yellow	25.0 x 33.5	25.0 x 12.7	4.0 - 7.0	6400	1
83256544	FLEXIMARK® Label LCK 35 YE-100	yellow	25.0 x 55.0	25.0 x 19.0	6.0 - 12.0	4000	1
83256546	FLEXIMARK® Label LCK 40 YE-100	yellow	25.0 x 94.0	25.0 x 25.4	8.0 - 21.0	2400	1

Last Update (12.02.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

FLEXIMARK® Wrapping label LCK

Article number	Article designation	Colour	Width x length (mm)	Labelling surface (mm)	For outer Ø (mm)	Markers / PU	PU
83256548	FLEXIMARK® Label LCK 45 YE-100	yellow	25.0 x 142.5	25.0 x 25.4	8.0 - 36.0	1600	1
83256550	FLEXIMARK® Label LCK 60 YE-100	yellow	50.0 x 56.0	50.0 x 19.0	6.0 - 12.0	2000	1
83256552	FLEXIMARK® Label LCK 65 YE-100	yellow	50.0 x 95.0	50.0 x 25.0	8.0 - 21.0	1200	1
83256554	FLEXIMARK® Label LCK 70 YE-100	yellow	50.0 x 142.5	50.0 x 25.0	8.0 - 36.0	800	1
83256543	FLEXIMARK® Label LCK 32 WH-100	white	25.0 x 33.5	25.0 x 12.0	4.0 - 7.0	6400	1
83256545	FLEXIMARK® Label LCK 35 WH-100	white	25.0 x 55.0	25.0 x 19.0	6.0 - 12.0	4000	1
83256547	FLEXIMARK® Label LCK 40 WH-100	white	25.0 x 94.0	25.0 x 25.0	8.0 - 21.0	2400	1
83256549	FLEXIMARK® Label LCK 45 WH-100	white	25.0 x 142.5	25.0 x 25.4	8.0 - 36.0	1600	1
83256551	FLEXIMARK® Label LCK 60 WH-100	white	50.0 x 56.0	50.0 x 19.0	6.0 - 12.0	2000	1
83256553	FLEXIMARK® Label LCK 65 WH-100	white	50.0 x 94.0	50.0 x 25.4	8.0 - 21.0	1200	1
83256555	FLEXIMARK® Label LCK 70 WH-100	white	50.0 x 142.5	50.0 x 25.4	8.0 - 36.0	800	1