

## FLEXIMARK® Wrapping labels TCK

FLEXIMARK® TCK wrapping labels are markers of vinyl with an protective transparent foil for marking cables with a thermal transfer printer



Solar Energy



Wind Energy



Good chemical resistance



Halogen-free



UV-resistant



Waterproof

### Benefits

A transparent film is wrapped around the cable and pasted over the printed field so that the printing is protected against abrasion, pollution and solvents

Resistant to chemicals, UV-light, moisture and oils (diesel oil, basic cleaning agent, sea water, ethanol,...)

Due to tight wrapping, space-saving

### Application range

For cable marking

### Note

Easy to print via FLEXIMARK® software Flexisoft and FLEXIMARK® thermal transfer printer SQUIX, EOS5 or EOS2

Recommended ribbon: R71 110-360 resin BK (article no. 83259609)

### Included

Delivered as a roll of labels

Last Update (21.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## FLEXIMARK® Wrapping labels TCK

### Technical Data

|                        |                                                                               |
|------------------------|-------------------------------------------------------------------------------|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC001288<br>ETIM 5.0 Class-Description: Labelling material |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC001288<br>ETIM 6.0 Class-Description: Labelling material |
| Adhesive:              | Acrylic-based permanent adhesive                                              |
| Colour delivered:      | White or yellow                                                               |
| Material:              | Halogen-free polyester<br>Thickness: 0.025 mm                                 |
| Temperature range:     | -40 °C to +125 °C<br>Minimum working temperature: +10 °C                      |

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

# FLEXIMARK® Wrapping labels TCK

| Article number | Article designation        | Colour | Width x length (mm) | Printable surface (W x H mm) | For Ø (mm) | Markers / PU | PU |
|----------------|----------------------------|--------|---------------------|------------------------------|------------|--------------|----|
| White version  |                            |        |                     |                              |            |              |    |
| 83259874       | FLEXIMARK® Label TCK 32 WH | white  | 25.0 x 33.5         | 25.0 x 12.7                  | 4.0 - 7.0  | 1200         | 1  |
| 83259875       | FLEXIMARK® Label TCK 35 WH | white  | 25.0 x 55.0         | 25.0 x 19.0                  | 6.0 - 12.0 | 1200         | 1  |
| 83259876       | FLEXIMARK® Label TCK 40 WH | white  | 25.0 x 94.0         | 25.0 x 25.0                  | 8.0 - 21.0 | 600          | 1  |
| 83259877       | FLEXIMARK® Label TCK 45 WH | white  | 25.0 x 142.5        | 25.0 x 25.0                  | 8.0 - 36.0 | 600          | 1  |
| 83259890       | FLEXIMARK® Label TCK 48 WH | white  | 34.0 x 93.0         | 34.0 x 25.4                  | 8.0 - 21.0 | 600          | 1  |
| 83259878       | FLEXIMARK® Label TCK 60 WH | white  | 50.0 x 56.0         | 50.0 x 19.0                  | 6.0 - 12.0 | 600          | 1  |
| 83259879       | FLEXIMARK® Label TCK 65 WH | white  | 50.0 x 94.0         | 50.0 x 25.4                  | 8.0 - 21.0 | 600          | 1  |
| 83259881       | FLEXIMARK® Label TCK 70 WH | white  | 50.0 x 142.5        | 50.0 x 25.4                  | 8.0 - 36.0 | 600          | 1  |
| Yellow version |                            |        |                     |                              |            |              |    |
| 83259882       | FLEXIMARK® Label TCK 32 YE | yellow | 25.0 x 33.5         | 25.0 x 12.7                  | 4.0 - 7.0  | 1200         | 1  |
| 83259883       | FLEXIMARK® Label TCK 35 YE | yellow | 25.0 x 55.0         | 25.0 x 19.0                  | 6.0 - 12.0 | 1200         | 1  |
| 83259884       | FLEXIMARK® Label TCK 40 YE | yellow | 25.0 x 94.0         | 25.0 x 25.0                  | 8.0 - 21.0 | 600          | 1  |
| 83259885       | FLEXIMARK® Label TCK 45 YE | yellow | 25.0 x 142.5        | 25.0 x 25.0                  | 8.0 - 36.0 | 600          | 1  |
| 83259889       | FLEXIMARK® Label TCK 48 YE | yellow | 34.0 x 93.0         | 34.0 x 25.4                  | 8.0 - 21.0 | 600          | 1  |
| 83259886       | FLEXIMARK® Label TCK 60 YE | yellow | 50.0 x 56.0         | 50.0 x 19.0                  | 6.0 - 12.0 | 600          | 1  |
| 83259887       | FLEXIMARK® Label TCK 65 YE | yellow | 50.0 x 94.0         | 50.0 x 25.4                  | 8.0 - 21.0 | 600          | 1  |
| 83259888       | FLEXIMARK® Label TCK 70 YE | yellow | 50.0 x 142.5        | 50.0 x 25.4                  | 8.0 - 36.0 | 600          | 1  |