

FLEXIMARK® Prohibition signs

Safety signs in accordance with ISO 7010 made of laminated polyester for long-term labeling

Info

All symbols according to ISO 7010



Halogen-free



UV-resistant

Benefits

Very resistant to UV, moisture, chemicals (e.g. glass cleaner, alcohol, oil)

Scratch resistant

Powerful adhesive

Application range

Control cabinet manufacturing

Mechanical engineering

Robotics

Safety marking in industrial environment

Indoor and outdoor applications

Product features

Self-adhesive labels

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001288

ETIM 5.0 Class-Description: Labelling material

On request:

Further dimensions and symbols

Colour delivered:

red

Material:

Laminated polyester (halogen-free)

Temperature range:

-40 °C to +150 °C

Processing: min. +10 °C

Last Update (26.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FLEXIMARK® Prohibition signs

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

FLEXIMARK® Prohibition signs

Article number	Article designation	Description	Dimension in mm	Markers / PU	PU
83880190	FLEXIMARK® P003 adh 25	No open flame; Fire, open ignition source and smoking prohibited	25	10	1
83880191	FLEXIMARK® P003 adh 50	No open flame; Fire, open ignition source and smoking prohibited	50	10	1
83880192	FLEXIMARK® P003 adh 100	No open flame; Fire, open ignition source and smoking prohibited	100	10	1
83880202	FLEXIMARK® P007 adh 25	No access for people with active implanted cardiac devices	25	10	1
83880203	FLEXIMARK® P007 adh 50	No access for people with active implanted cardiac devices	50	10	1
83880204	FLEXIMARK® P007 adh 100	No access for people with active implanted cardiac devices	100	10	1
83880253	FLEXIMARK® P024 adh 25	Do not walk or stand here	25	10	1
83880254	FLEXIMARK® P024 adh 50	Do not walk or stand here	50	10	1
83880255	FLEXIMARK® P024 adh 100	Do not walk or stand here	100	10	1
83880274	FLEXIMARK® P031 adh 25	Do not alter the state of the switch	25	10	1
83880275	FLEXIMARK® P031 adh 50	Do not alter the state of the switch	50	10	1
83880276	FLEXIMARK® P031 adh 100	Do not alter the state of the switch	100	10	1

FLEXIMARK® Prohibition signs

