

FLEXIMARK® Warning signs

Safety signs in accordance with ISO 7010 made of laminated polyester for long-term labeling

Info

All symbols according to ISO 7010



Suitable for outdoor use



Good chemical resistance



Halogen-free



Temperature-resistant



UV-resistant

Benefits

Very resistant to UV, moisture, chemicals (e.g. glass cleaner, alcohol, oil)

Scratch resistant

Powerful adhesive

Application range

Control cabinet manufacturing

Mechanical engineering

Robotics

Safety marking in industrial environment

Indoor and outdoor applications

Product features

Self-adhesive labels

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001288

Last Update (07.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FLEXIMARK® Warning signs

On request:	ETIM 5.0 Class-Description: Labelling material
Colour delivered:	Further dimensions and symbols
Material:	Yellow
Temperature range:	Laminated polyester (halogen-free)
	-40 °C to +150 °C
	Processing: min. +10 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

FLEXIMARK® Warning signs

Article number	Article designation	Description	Dimension in mm	Markers / PU	PU
83880016	FLEXIMARK® W001 adh 25	General warning sign	25	10	1
83880017	FLEXIMARK® W001 adh 50	General warning sign	50	10	1
83880018	FLEXIMARK® W001 adh 100	General warning sign	100	10	1
83880019	FLEXIMARK® W002 adh 25	Warning; explosive material	25	10	1
83880020	FLEXIMARK® W002 adh 50	Warning; explosive material	50	10	1
83880021	FLEXIMARK® W002 adh 100	Warning; explosive material	100	10	1
83880049	FLEXIMARK® W012 adh 25	Warning; Electricity	25	10	1
83880050	FLEXIMARK® W012 adh 50	Warning; Electricity	50	10	1
83880051	FLEXIMARK® W012 adh 100	Warning; Electricity	100	10	1
83880064	FLEXIMARK® W017 adh 25	Warning; Hot surface	25	10	1
83880065	FLEXIMARK® W017 adh 50	Warning; Hot surface	50	10	1
83880066	FLEXIMARK® W017 adh 100	Warning; Hot surface	100	10	1
83880076	FLEXIMARK® W021 adh 25	Warning; Flammable material	25	10	1
83880077	FLEXIMARK® W021 adh 50	Warning; Flammable material	50	10	1
83880078	FLEXIMARK® W021 adh 100	Warning; Flammable material	100	10	1
83880088	FLEXIMARK® W025 adh 25	Warning; Counterrotating rollers	25	10	1
83880089	FLEXIMARK® W025 adh 50	Warning; Counterrotating rollers	50	10	1
83880090	FLEXIMARK® W025 adh 100	Warning; Counterrotating rollers	100	10	1
83880091	FLEXIMARK® W026 adh 25	Warning; Battery charging	25	10	1
83880092	FLEXIMARK® W026 adh 50	Warning; Battery charging	50	10	1
83880093	FLEXIMARK® W026 adh 100	Warning; Battery charging	100	10	1

Last Update (07.09.2020)

©2020 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

FLEXIMARK® Warning signs

