

SILVYN® LCS-M

SILVYN® LCS-M is a swivelling nickel-plated brass conduit fitting that offers IP65 protection due to its integrated pressure seal



Corrosion-resistant



Maximum vibration protection



Oil-resistant



Robust

Benefits

High tensile strength
Vibration protection
Enhanced sealing

Application range

In combination with protective conduit:
SILVYN® LCC-2 / LCCH-2
Applications with high mechanical stress
Used in areas where liquids are present

Product Make-up

Metric connection thread
Hexagonal collar with torsion element
Threaded sleeve
Cap nut

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001180

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® LCS-M

Classification ETIM 6:	ETIM 5.0 Class-Description: Screw connection for protective metallic hose ETIM 6.0 Class-ID: EC001180 ETIM 6.0 Class-Description: Screw connection for protective metallic hose
Certifications:	IEC EN 61386-23
Material:	Body: nickel-plated brass Seal: PA compression seal
Protection rating:	IP 65
Temperature range:	-50 °C to +135 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® LCS-M

Article number	Metric size	SW 1/2 mm	Overall length mm	Thread length mm	Suitable for SILVYN® LCC-2/LCCH-2	Pieces / PU
SILVYN® LCS-M						
55503470	16 x 1.5/1	20 / 22	39	10	12	10
55503471	16 x 1.5/2	24 / 26	40.9	10	16	10
55503472	20 x 1.5/1	24 / 26	41	10	16	10
55503473	20 x 1.5/2	26 / 29	41.8	10	20	10
55503474	25 x 1.5	33 / 35	50.7	12	25	10
55503475	32 x 1.5	40 / 42	56.9	13	32	2