# SILVYN® LGS-2

SILVYN® LGS-2 is a swivelling nickel-plated brass conduit fitting for installation with torsional movements



Corrosion-resistant

Mechanical resistance

Oil-resistant

Space requirement

Robust

## Benefits

For rotating applications
High tensile strength
Space-saving

## Application range

In combination with protective conduit:
SILVYN® LCC-2
SILVYN® LCCH-2
Applications with high mechanical stress
Outdoors

## Product Make-up

PG connection thread
Hexagonal collar with torsion element
Cap nut

Last Update (21.05.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

# SILVYN® LGS-2

## Technical Data

| | |
|---|---|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC001180<br>ETIM 5.0 Class-Description: Screw connection for protective metallic hose |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC001180<br>ETIM 6.0 Class-Description: Screw connection for protective metallic hose |
| Norm references / Approvals: | IEC EN 61386-23 |
| Material: | Nickel-plated brass |
| Protection rating: | IP 54 |
| Temperature range: | -50 °C to +300 °C |

## Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.


©2025 Lapp Group - Technical changes reserved

LAPP

# SILVYN® LGS-2

PRODUCT INFORMATION

| Article number | Metric size | SW wrench size mm | Overall length mm | Thread length mm | Suitable for SILVYN® LCC-2 / LCCH-2 | Pieces / PU |
|---|---|---|---|---|---|---|
| SILVYN® LGS-2 | | | | | | |
| 55502710 | 7 | 13 | 32 | 7 | 10 | 10 |
| 55502720 | 9 | 17 | 38 | 10 | 12 | 10 |
| 55502730 | 11 | 22 | 38 | 10 | 16 | 10 |
| 55502740 | 13.5 | 24 | 39 | 12 | 20 | 10 |
| 55502750 | 16 | 24 | 44 | 12 | 20 | 10 |
| 55502760 | 21 | 29 | 50 | 12 | 25 | 10 |
| 55502770 | 29 | 36 | 56 | 12 | 32 | 10 |
| 55502780 | 36 | 48 | 59 | 12 | 40 | 4 |
| 55502790 | 48 | 70 | 61.2 | 16 | 63 | 1 |

Last Update (21.05.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16