

## SILVYN® FCE-M

Nickel-plated brass fitting with space-saving dimensions in various designs

### Info

Space-saving due to compact dimensions.



### Benefits

- High mechanical stability
- High tensile strength
- Space-saving application
- Corrosion-resistant

### Application range

In combination with protective conduit:  
 SILVYN® FCE-V0  
 SILVYN® FCE-LFH

### Product Make-up

- Metric connection thread
- Hexagonal collar
- Threaded sleeve
- Cap nut

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001180

ETIM 5.0 Class-Description: Screw connection for protective metallic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001180

ETIM 6.0 Class-Description: Screw connection for protective metallic hose

Material:

SILVYN® FCE COMPACT

Metal parts: nickel-plated brass

Sealings: NBR

SILVYN® FCE-F, FCE-S

Nickel-plated brass

Protection rating:

SILVYN® FCE COMPACT: IP 68

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® FCE-M

Temperature range:

SILVYN® FCE-F, FCE-S: IP 54

SILVYN® FCE COMPACT: -45°C to +105°C

SILVYN® FCE-F, FCE-S: -55°C to +260°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® FCE-M**

Article number	Metric size	Suitable for SILVYN® FCE	Pieces / PU
<b>SILVYN® FCE COMPACT M</b>			
55503624	12 x 1.5	13	10
55503625	16 x 1.5	16	10
55503626	20 x 1.5	16	10
55503627	20 x 1.5	20	10
55503628	25 x 1.5	25	5
61803855	32 x 1.5	32	5
61803856	40 x 1.5	40	2
<b>SILVYN® FCE COMPACT 90° M</b>			
61803860	16 x 1.5	16	10
61803861	20 x 1.5	16	10
61803862	20 x 1.5	20	10
61803863	25 x 1.5	25	5
61803864	32 x 1.5	32	5
<b>SILVYN® FCE-F M</b>			
55503600	10 x 1.0	10	10
55503601	12 x 1.5	10	10
55503602	12 x 1.5	13	10
55503603	16 x 1.5	13	10
55503604	16 x 1.5	16	10
55503605	20 x 1.5	16	10
55503606	20 x 1.5	20	10
55503607	25 x 1.5	25	5
55503608	32 x 1.5	32	5
55503609	40 x 1.5	40	2
55503610	50 x 1.5	50	2
55503611	63 x 1.5	50	2
<b>SILVYN® FCE-S M</b>			
55503612	10 x 1.0	10	10
55503613	12 x 1.5	10	10
55503614	12 x 1.5	13	10
55503615	16 x 1.5	13	10
55503616	16 x 1.5	16	10
55503617	20 x 1.5	16	10
55503618	20 x 1.5	20	10

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16



## SILVYN® FCE-M

Article number	Metric size	Suitable for SILVYN® FCE	Pieces / PU
55503619	25 x 1.5	25	5
55503620	32 x 1.5	32	5
55503621	40 x 1.5	40	2
55503622	50 x 1.5	50	2
55503623	63 x 1.5	50	2

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16

**SILVYN® FCE-M**

