

## SILVYN® EC

SILVYN® EC - end cap for parallel corrugated conduits



Wide clamping range



Low weight



Reliability



Temperature-resistant



UV-resistant

### Benefits

Cable damage can be prevented

Additional sealing

Easy to assemble

### Application range

In combination with protective conduit:

SILVYN® FPAS

Intersection or end sleeve

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000519

ETIM 5.0 Class-Description: Terminal sleeve for protective hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000519

ETIM 6.0 Class-Description: Terminal sleeve for protective hose

On request:

SILVYN® REC for FPAS67

Colour delivered:

Black (RAL 9005), UV-resistant

Material:

NEC: PA66

REC: TPE

Temperature range:

NEC: -50 °C to +135 °C

Last Update (22.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**SILVYN® EC**

REC: -50°C to +120°C

**Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® EC**

| Article number | Nominal size | Clamping range in mm | Clear opening (mm) | Suitable for SILVYN® FPAS | Pieces / PU |
|----------------|--------------|----------------------|--------------------|---------------------------|-------------|
| SILVYN® NEC    |              |                      |                    |                           |             |
| 55507097       | 16           | -                    | 10.5               | 16                        | 10          |
| 55507098       | 21           | -                    | 15                 | 21                        | 10          |
| 55507099       | 28           | -                    | 20                 | 28                        | 10          |
| 55507100       | 34           | -                    | 25.5               | 34                        | 10          |
| 55507101       | 42           | -                    | 32                 | 42                        | 10          |
| 55507102       | 54           | -                    | 43.5               | 54                        | 10          |
| SILVYN® REC    |              |                      |                    |                           |             |
| 55507040       | 10           | 3 - 7                | -                  | 10                        | 10          |
| 55507041       | 13           | 3 - 7                | -                  | 13                        | 10          |
| 55507042       | 16           | 3 - 11               | -                  | 16                        | 10          |
| 55507043       | 21           | 3 - 15               | -                  | 21                        | 10          |
| 55507044       | 28           | 3 - 21               | -                  | 28                        | 10          |
| 55507045       | 34           | 3 - 25               | -                  | 34                        | 10          |
| 55507046       | 42           | 5 - 34               | -                  | 42                        | 10          |
| 55507047       | 54           | 5 - 46               | -                  | 54                        | 10          |

## SILVYN® EC

