

SILVYN® FLEXILOK 90° M

SILVYN® FLEXILOK 90° M - angled metric threaded conduit fitting

Info

extremely economical
90° elbow allows easy installation
Small purchasing unit



Halogen-free



Assembly time



Space requirement



Temperature-resistant

Benefits

Fast assembly
Easy to assemble
Cost-effective conduit gland
No loose parts
New space-saving design

Application range

Mechanical engineering
Control cabinet manufacturing
Moving applications
Applications with limited space
Building Installation

Last Update (20.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® FLEXILOK 90° M

Product features

In black colour UV-resistant and weather-proofed
One-piece slim design
Halogen and cadmium-free

Norm references / Approvals

UL FILENUMBER E308201

Product Make-up

Metric connection thread
90° elbow
Special clamping system

Note

Removeable with a screwdriver
PG threaded versions are to be found in the online catalogue

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Norm references / Approvals:	IEC EN 61386-23
Colour delivered:	Grey (RAL 7031) Black (RAL 9005), UV-resistant
Material:	PA66 Halogen-free
Protection rating:	IP 66
Temperature range:	-40°C to +120°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® FLEXILOK 90° M

Article number	Metric size	Thread length mm	Suitable for SILVYN® FPAS	Suitable for conduit Ø (mm)	Pieces / PU
SILVYN® FLEXILOK 90° M black					
68100100	16 x 1.5	12	FPAS 16	15,8	10
68100105	20 x 1.5	13	FPAS 16	15,8	10
68100106	20 x 1.5	13	FPAS 20	20	10
68100110	20 x 1.5	13	FPAS 21	21,2	10
68100114	25 x 1.5	15	FPAS 25	25	10
68100115	25 x 1.5	15	FPAS 28	28,5	10
68100119	32 x 1.5	16	FPAS 32	32	10
68100120	32 x 1.5	16	FPAS 34	34,5	10
SILVYN® FLEXILOK 90° M grey					
68100125	16 x 1.5	12	FPAS 16	15,8	10
68100130	20 x 1.5	13	FPAS 16	15,8	10
68100131	20 x 1.5	13	FPAS 20	20	10
68100135	20 x 1.5	13	FPAS 21	21,2	10
68100139	25 x 1.5	15	FPAS 25	25	10
68100140	25 x 1.5	15	FPAS 28	28,5	10
68100144	32 x 1.5	16	FPAS 32	32	10
68100145	32 x 1.5	16	FPAS 34	34,5	10

Last Update (20.09.2020)

©2020 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03.16