

SILVYN® FLEXILOK M

SILVYN® FLEXILOK M - metric threaded conduit fitting

Info

extremely economical
Small purchasing unit



Halogen-free



Assembly time



Space requirement



Temperature-resistant

Benefits

Fast assembly
Easy to assemble
Cost-effective conduit gland
No loose parts
New space-saving design

Application range

Mechanical engineering
Control cabinet manufacturing
Moving applications
Applications with limited space
Building Installation

Product features

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® FLEXILOK M

In black colour UV-resistant and weather-proofed
One-piece slim design
Halogen and cadmium-free

Norm references / Approvals

UL FILENUMBER E308201

Product Make-up

Metric connection thread
One-piece body
Special clamping system

Note

Removeable with a screwdriver
PG threaded versions are to be found in the online catalogue

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Norm references / Approvals:	IEC EN 61386-23
Colour delivered:	Grey (RAL 7031) Black (RAL 9005), UV-resistant
Material:	PA66 Halogen-free
Protection rating:	IP 66
Temperature range:	-40 °C to +120 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® FLEXILOK M

Article number	Metric size	Thread length mm	Suitable for SILVYN® FPAS	Suitable for conduit Ø (mm)	Pieces / PU
SILVYN® FLEXILOK M black					
65500403	12 x 1.5	9	FPAS 10	10,0	10
65500405	16 x 1.5	12	FPAS 13	13,0	10
65500425	16 x 1.5	12	FPAS 16	15,8	10
65500415	20 x 1.5	14	FPAS 13	13,0	10
65500435	20 x 1.5	14	FPAS 16	15,8	10
65500436	20 x 1.5	14	FPAS 20	20	10
65500445	20 x 1.5	14	FPAS 21	21,2	10
65500456	25 x 1.5	15	FPAS 25	25	10
65500455	25 x 1.5	15	FPAS 28	28,5	10
65500464	32 x 1.5	16	FPAS 32	32	10
65500465	32 x 1.5	16	FPAS 34	34,5	10
65500458	40 x 1.5	16	FPAS 42	42,5	2
65500459	50 x 1.5	16	FPAS 54	54,5	1
65500468	63 x 1.5	16	FPAS 54	54,5	1
SILVYN® FLEXILOK M grey					
65500404	12 x 1.5	9	FPAS 10	10,0	10
65500600	16 x 1.5	12	FPAS 13	13,0	10
65500420	16 x 1.5	12	FPAS 16	15,8	10
65500410	20 x 1.5	14	FPAS 13	13,0	10
65500430	20 x 1.5	14	FPAS 16	15,8	10
65500431	20 x 1.5	14	FPAS 20	20	10
65500440	20 x 1.5	14	FPAS 21	21,2	10
65500454	25 x 1.5	15	FPAS 25	25	10
65500610	25 x 1.5	15	FPAS 28	28,5	10
65500451	32 x 1.5	16	FPAS 32	32	10
65500460	32 x 1.5	16	FPAS 34	34,5	10
65500466	40 x 1.5	16	FPAS 42	42,5	2
65500467	50 x 1.5	16	FPAS 54	54,5	1
65500469	63 x 1.5	16	FPAS 54	54,5	1

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16