

SILVYN® FLEXILOK PG

SILVYN® FLEXILOK PG - PG threaded conduit fitting

Info

extremely economical
Small purchasing unit



Halogen-free



Assembly time



Space requirement



Temperature-resistant

Benefits

Fast assembly
Easy to assemble
Cost-effective conduit gland
No loose parts
New space-saving design

Application range

Mechanical engineering
Control cabinet manufacturing
Moving applications
Applications with limited space
Building Installation

Product features

Last Update (23.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® FLEXILOK PG

In black colour UV-resistant and weather-proofed
One-piece slim design
Halogen and cadmium-free

Norm references / Approvals

UL FILENUMBER E308201

Product Make-up

PG connection thread
One-piece body
Special clamping system

Note

Removeable with a screwdriver

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Norm references / Approvals:	IEC EN 61386-23
On request:	PG 7 for FPAS 10 PG 36 for FPAS 42 PG 48 for FPAS 54
Colour delivered:	Grey (RAL 7031) Black (RAL 9005), UV-resistant
Material:	PA66 Halogen-free
Protection rating:	IP 66
Temperature range:	-40°C to +120°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® FLEXILOK PG

Article number	Thread length mm	Suitable for SILVYN® FPAS	Suitable for conduit ØØ (mm)	Pieces / PU
SILVYN® FLEXILOK PG black				
65500475	10	FPAS 13	13,0	10
65500495	10	FPAS 16	15,8	10
65500485	10	FPAS 13	13,0	10
65500395	10	FPAS 16	15,8	10
68100055	10	FPAS 16	15,8	10
68100075	10	FPAS 21	21,2	10
68100065	11	FPAS 16	15,8	10
68100085	11	FPAS 21	21,2	10
68100095	12	FPAS 28	28,5	10
68880005	12	FPAS 34	34,5	10
SILVYN® FLEXILOK PG grey				
65500470	10	FPAS 13	13,0	10
65500490	10	FPAS 16	15,8	10
65500480	10	FPAS 13	13,0	10
65500390	10	FPAS 16	15,8	10
68100050	10	FPAS 16	15,8	10
68100060	11	FPAS 16	15,8	10
68100080	11	FPAS 21	21,2	10
68100090	12	FPAS 28	28,5	10
65500620	12	FPAS 34	34,5	10

Last Update (23.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16