

## SILVYN® FPAG 90° M

SILVYN® FPAG 90° M - conduit fitting for SILVYN® FPAS



Maximum vibration protection



Assembly time



Space requirement



Temperature-resistant



Variety of approval certifications

### Benefits

90° elbow allows easy installation  
Fast assembly  
High-tensile  
Sealing  
Vibration protection

### Application range

In combination with protective conduit:  
SILVYN® FPAS  
Applications with strong vibrations  
For applications with limited space

### Product features

In black colour UV-resistant and weather-proofed  
Removeable with a screwdriver

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® FPAG 90° M

### Norm references / Approvals

UL FILENUMBER E308201

### Product Make-up

Metric connection thread

90° elbow

Body

Upper part with integrated all-round toothing

### Note

PG threaded versions are to be found in the online catalogue

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Certifications:	IEC EN 61386-23
Colour delivered:	Grey (RAL 7031) Black (RAL 9005), UV-resistant
Material:	PA66 Halogen-free
Protection rating:	IP66
Temperature range:	-50°C to +135°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® FPAG 90° M**

Article number	Metric size	Suitable for SILVYN® FPAS	Pieces / PU
<b>SILVYN® FPAG 90° M black</b>			
55506485	12 x 1.5	10	10
55506495	16 x 1.5	13	10
55506505	16 x 1.5	16	10
55506515	20 x 1.5	16	10
55507075	20 x 1.5	18	10
55506526	20 x 1.5	20	10
55506525	20 x 1.5	21	10
55506536	25 x 1.5	25	10
55506535	25 x 1.5	28	10
55506545	32 x 1.5	34	10
55507085	40 x 1.5	42	1
55506555	50 x 1.5	42	1
55506565	50 x 1.5	54	1
55506575	63 x 1.5	54	1
55507095	63 x 1.5	67	1
<b>SILVYN® FPAG 90° M grey</b>			
55506480	12 x 1.5	10	10
55506490	16 x 1.5	13	10
55506500	16 x 1.5	16	10
55506510	20 x 1.5	16	10
55507070	20 x 1.5	18	10
55506521	20 x 1.5	20	10
55506520	20 x 1.5	21	10
55506531	25 x 1.5	25	10
55506530	25 x 1.5	28	10
55506540	32 x 1.5	34	10
55507080	40 x 1.5	42	1
55506550	50 x 1.5	42	1
55506560	50 x 1.5	54	1
55506570	63 x 1.5	54	1
55507090	63 x 1.5	67	1

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16