

SILVYN® FPAG PG

SILVYN® FPAG PG - conduit fitting for SILVYN® FPAS



Halogen-free



Maximum vibration protection



Assembly time



Optimum strain relief



Temperature-resistant



Variety of approval certifications

Benefits

Fast assembly
High-tensile
Sealing
Vibration protection

Application range

In combination with protective conduit:
SILVYN® FPAS
Applications with strong vibrations

Product features

In black colour UV-resistant and weather-proofed
Removeable with a screwdriver

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® FPAG PG

Norm references / Approvals

UL FILENUMBER E308201

Product Make-up

PG connection thread

Body

Upper part with integrated all-round toothing

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose

Certifications:

IEC EN 61386-23

Colour delivered:

Grey (RAL 7031)

Black (RAL 9005), UV-resistant

Material:

PA66

Halogen-free

Protection rating:

IP 66

Temperature range:

-50°C to +135°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® FPAG PG

Article number	Suitable for SILVYN® FPAS	Pieces / PU
SILVYN® FPAG PG black		
55506585	10	10
55506595	10	10
55506605	13	10
55506615	16	10
55506625	16	10
55506635	16	10
55506645	18	10
55506995	21	10
55506655	21	10
55506665	28	10
55506675	34	10
55506685	42	2
55506695	54	2
55506705	67	2
SILVYN® FPAG PG grey		
55506580	10	10
55506590	10	10
55506600	13	10
55506610	16	10
55506620	16	10
55506630	16	10
55506640	18	10
55506990	21	10
55506650	21	10
55506660	28	10
55506670	34	10
55506680	42	2
55506690	54	2
55506700	67	2