

SILVYN® FPAX P

SILVYN® FPAX P - plug for T/Y piece



Benefits

Stop Plug for the SILVYN® FPAX T/Y system

Application range

In combination with protective conduit:
SILVYN® FPAS

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001172 ETIM 5.0 Class-Description: Coupler for corrugated plastic hoses
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001172 ETIM 6.0 Class-Description: Coupler for corrugated plastic hoses
Colour delivered:	Black (RAL 9005), UV-resistant
Material:	PA66 Halogen-free Polyester Elastomer
Protection rating:	IP66 IP67 IP68 (2 bar) IP69
Temperature range:	-50°C to +135°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.



SILVYN® FPAX P

Article number	Nominal size	Suitable for SILVYN® FPAX T/Y	Pieces / PU
SILVYN® FPAX P			
55507370	16	16	5
55507371	21	21	5
55507372	28	28	5
55507373	34	34	3

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16