

SILVYN® FPAX R

SILVYN® FPAX R - reducer for T/Y piece

Info

Reducer for the SILVYN® FPAX T/Y system



Wide clamping range



Maximum vibration protection



Space requirement



Reliability



UV-resistant

Benefits

Reducer for the SILVYN® FPAX T/Y system

Application range

In combination with protective conduit:
SILVYN® FPAS

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001172

ETIM 5.0 Class-Description: Coupler for corrugated plastic hoses

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001172

ETIM 6.0 Class-Description: Coupler for corrugated plastic hoses

Colour delivered:

Black (RAL 9005), UV-resistant

Material:

PA66

Halogen-free

Polyester Elastomer

Last Update (25.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® FPAX R

Protection rating:	IP66
	IP67
	IP68 (2 bar)
	IP69
Temperature range:	-50 °C to +135 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® FPAX R

Article number	Nominal size	Suitable for SILVYN® FPAX T/Y	Suitable for SILVYN® FPAS	Pieces / PU
SILVYN® FPAX R				
55507360	16-13	16	13	5
55507361	21-16	21	16	5
55507363	28-16	28	16	5
55507362	28-21	28	21	5
55507366	34-16	34	16	5
55507365	34-21	34	21	5
55507364	34-28	34	28	5
55507369	42-21	42	21	3
55507368	42-28	42	28	3
55507367	42-34	42	34	3

Last Update (25.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16