

SILVYN® FPAX T

SILVYN® FPAX T - divider in T-shape for SILVYN® FPAS



Benefits

Fast assembly
High tensile strength
Watertight
Vibration protection

Application range

In combination with protective conduit:
SILVYN® FPAS

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001172 ETIM 5.0 Class-Description: Coupler for corrugated plastic hoses
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001172 ETIM 6.0 Class-Description: Coupler for corrugated plastic hoses
Colour delivered:	Black (RAL 9005), UV-resistant
Material:	PA66 Halogen-free Polyester Elastomer
Protection rating:	IP66 IP67 IP68 (2 bar) IP69
Temperature range:	-50 °C to +135 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® FPAX T

Article number	Nominal size	Hole Ø (mm)	Suitable for SILVYN® FPAS	Pieces / PU
SILVYN® FPAX T				
55507340	16	6	16	3
55507341	21	6	21	3
55507342	28	6	28	3
55507343	34	7	34	3
55507344	42	7	42	3