

SILVYN® gasket AFG-PA / AFW-PA

SILVYN® gasket AFG-PA / AFW-PA is a sealing ring for usage with the connection flange for large diameters



Assembly time



Robust



Reliability

Benefits

Increases the IP degree of protection of SILVYN® AFG-PA and SILVYN® AFW-PA

Application range

In combination with protective conduit

SILVYN® MAXI PA

Mechanical engineering

Bundling and guiding of cables and wires

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000781

ETIM 5.0 Class-Description: Sealing for hose screw connection

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000781

ETIM 6.0 Class-Description: Sealing for hose screw connection

Colour delivered:

Grey (RAL 7001)

Black (RAL 9005), UV-resistant

Material:

PA6

Halogen-free

Protection rating:

IP 54

IP 65 with AFG-PA/AFW-PA seal

Temperature range:

-40 °C to +115 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Last Update (26.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® gasket AFG-PA / AFW-PA

Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® gasket AFG-PA / AFW-PA

Article number	Nominal size	Pieces / PU
SILVYN® seal for AFG-PA, AFW-PA		
55001082	70	1
55001083	95	1

Last Update (26.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16