

SILVYN® HG-M

SILVYN® HG-M - conduit fitting for SILVYN® HCC



UV-resistant

Benefits

Easy to disassemble
High-tensile
Sealing

Application range

In combination with protective conduit
SILVYN® HCC

Product Make-up

Metric connection thread
Body with sealing and clamping ring
Cap nut

Note

UV-resistant and weather-resistant

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose

Colour delivered:

Black (RAL 9005), UV-resistant

Material:

PA6

Protection rating:

IP 65

Temperature range:

-25°C to +100°C

Last Update (27.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® HG-M

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® HG-M

Article number	Article designation	Overall length mm	Thread length mm	Suitable for SILVYN® HCC	Pieces / PU
55501650	40 x 1,5	53	15	40	20
55501660	50 x 1,5	57.4	15	50	16
55501670	63 x 1,5	74	20	63	8