

## SILVYN® SPLIT GMP-M

SILVYN® SPLIT GMP-M is a divisible counter nut for subsequent installation with the divisible conduit SILVYN® SPLIT



Halogen-free



Assembly time



Temperature-resistant



UV-resistant

### Benefits

Fast assembly  
Easy to disassemble

### Note

UV-resistant and weather-resistant

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose

Colour delivered:

Black (RAL 9005), UV-resistant

Material:

Halogen-free PA

Temperature range:

-40°C to +120°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (16.02.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**SILVYN® SPLIT GMP-M**

Article number	Metric size	Pieces / PU
SILVYN® SPLIT GMP-M (metric counter nut)		
61806686	16 x 1.5	100
61806688	25 x 1.5	50
61806689	32 x 1.5	50
61806691	40 x 1.5	25
61806687	20 x 1.5	100
61806692	50 x 1.5	25

Last Update (16.02.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03.16