FIPLOCK® ONE Conduit holder (stackable)

Conduit fitting system for highest requirements, suitable for FIPLOCK® PA6 / PA12

FIPLOCK® ONE Conduit holder (stackable)

Info
New conduit fitting system with innovative locking system



Rail

Good chemical resistance

Flame-retardant

Halogen-free

Cold-resistant

Maximum vibration protection

Mechanical resistance

Assembly time

Low weight

Last Update (13.10.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FIPLOCK® ONE Conduit holder (stackable)

Optimum strain relief

Robust

Reliability

UV-resistant

Waterproof

Benefits

Very high tensile strength due to all around tooth system
Ensures mounting safety due to integrated coding system
Excellent IP rating
Cost-saving due to quick and easy installation

Application range

Suitable for FIPLOCK® PA6 / PA12
Demand of increased liquid tightness
For indoor and outdoor use

Product features

All around locking mechanism due to 360° tooth system
Locking mechanism with integrated coding system
Extended sealing range across multiple corrugated conduit waves

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Certifications:	IEC EN 61386-23 EN 45545-2 HL3
Colour delivered:	Grey (RAL 7005) Black (RAL 9005), UV-resistant
Material:	PA 6 Halogen-free Fire behaviour according to UL 94V-0
Protection rating:	IP66/IP67/IP68/IP69
Temperature range:	-45°C to +120°C

Last Update (13.10.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FIPLOCK® ONE Conduit holder (stackable)

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (13.10.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FIPLOCK® ONE Conduit holder (stackable)

Article number	Nominal size	Hole Ø (mm)	Design	Suitable for FIPLOCK® PA6 / PA12	Colour	Pieces / PU
Conduit mounting clamp						
61805116	17	8.5	Single	17	black	10
61805117	23	8.5	Single	23	black	6
61805118	29	8.5	Single	29	black	6
61805119	36	8.5	Single	36	black	4
61805120	48	8.5	Single	48	black	4
61805121	56	8.5	Single	56	black	4
Conduit mounting clamp with ball joint						
61805122	12	8.5	Single	12	black	10
61805123	17	8.5	Single	17	black	6
61805124	23	8.5	Single	23	black	6
61805125	29	8.5	Single	29	black	4
61805126	36	8.5	Single	36	black	4
61805127	48	8.5	Single	48	black	4
Multiple conduit mounting rail						
61805128	2x 36	8.5	Double	36	black	4
61805129	2x 48	8.5	Double	48	black	4
61805130	3x 36	8.5	Triple	36	black	4
61805131	3x 48	8.5	Triple	48	black	4
61805132	4x 36	8.5	Quadruple	36	black	4
61805133	4x 48	8.5	Quadruple	48	black	4

Last Update (13.10.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FIPLOCK® ONE Conduit holder (stackable)

Last Update (13.10.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16