

## FIPLOCK® ONE ST-NPT

Conduit fitting system for highest requirements, suitable for FIPLOCK® PA6 / PA12

FIPLOCK® ONE ST-NPT

### Info

New conduit fitting system with innovative locking system  
Integrated SKINTOP® cable strain relief



Rail



Good chemical resistance



Flame-retardant



Halogen-free



Cold-resistant



Maximum vibration protection



Mechanical resistance



Assembly time



Low weight

Last Update (26.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## FIPLOCK® ONE ST-NPT



Optimum strain relief



Robust



Reliability



UV-resistant



Waterproof



### Benefits

Very high tensile strength due to all around tooth system  
 Ensures mounting safety due to integrated coding system  
 Excellent IP rating  
 Cost-saving due to quick and easy installation

### Application range

Suitable for FIPLOCK® PA6 / PA12  
 Demand of increased liquid tightness  
 For indoor and outdoor use

### Product features

All around locking mechanism due to 360° tooth system  
 Locking mechanism with integrated coding system  
 Extended sealing range across multiple corrugated conduit waves  
 Cable strain relief

### Technical Data

|                        |   |
|------------------------|---|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC001176<br>ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC001176<br>ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose |
| Certifications:        | IEC EN 61386-23<br>EN 45545-2 HL3   |
| Colour delivered:      | Grey (RAL 7005)<br>Black (RAL 9005), UV-resistant   |
| Material:              | PA 6<br>Halogen-free<br>Fire behaviour according to UL 94V-0  |
| Protection rating:     | IP66/IP67/IP68/IP69   |
| Temperature range:     | -45°C to +120°C   |

Last Update (26.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## FIPLOCK® ONE ST-NPT

**Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**FIPLock® ONE ST-NPT**

| Article number            | Nominal size | Clamping range in mm | SW 1/2 mm   | Thread length mm | Suitable for FIPLock® PA6 / PA12 | Colour | Pieces / PU |
|---------------------------|--------------|----------------------|-------------|------------------|----------------------------------|--------|-------------|
| FIPLock® ONE ST-NPT black |              |                      |             |                  |                                  |        |             |
| 61804861                  | NPT 3/8"     | 3.5 - 8.0            | 19.0 / 20.0 | 15               | 10                               | black  | 10          |
| 61804862                  | NPT 3/8"     | 3.5 - 8.0            | 19.0 / 22.0 | 15               | 12                               | black  | 10          |
| 61804863                  | NPT 1/2"     | 5.0 - 12.0           | 24.0 / 22.0 | 15               | 12                               | black  | 10          |
| 61804864                  | NPT 1/2"     | 5.0 - 12.0           | 24.0 / 27.0 | 15               | 17                               | black  | 10          |
| 61804865                  | NPT 3/4"     | 13.0 - 18.0          | 33.0 / 36.0 | 15               | 23                               | black  | 6           |
| 61804866                  | NPT 1"       | 14.0 - 25.0          | 42.0 / 41.0 | 15               | 29                               | black  | 6           |
| FIPLock® ONE ST-NPT grey  |              |                      |             |                  |                                  |        |             |
| 61804867                  | NPT 3/8"     | 3.5 - 8.0            | 19.0 / 20.0 | 15               | 10                               | grey   | 10          |
| 61804868                  | NPT 3/8"     | 3.5 - 8.0            | 19.0 / 22.0 | 15               | 12                               | grey   | 10          |
| 61804869                  | NPT 1/2"     | 5.0 - 12.0           | 24.0 / 22.0 | 15               | 12                               | grey   | 10          |
| 61804871                  | NPT 1/2"     | 5.0 - 12.0           | 24.0 / 27.0 | 15               | 17                               | grey   | 10          |
| 61804872                  | NPT 3/4"     | 13.0 - 18.0          | 33.0 / 36.0 | 15               | 23                               | grey   | 6           |
| 61804873                  | NPT 1"       | 14.0 - 25.0          | 42.0 / 41.0 | 15               | 29                               | grey   | 6           |

Last Update (26.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16