

FIPLOCK® ONE ST-PG

Conduit fitting system for highest requirements, suitable for FIPLOCK® PA6 / PA12

FIPLOCK® ONE ST-PG

Info

New conduit fitting system with innovative locking system



Rail



Good chemical resistance



Flame-retardant



Halogen-free



Cold-resistant



Maximum vibration protection



Mechanical resistance



Assembly time



Low weight

Last Update (17.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FIPLOCK® ONE ST-PG



Optimum strain relief



Robust



Reliability



UV-resistant



Waterproof



Benefits

Very high tensile strength due to all around tooth system
 Ensures mounting safety due to integrated coding system
 Excellent IP rating
 Cost-saving due to quick and easy installation

Application range

Suitable for FIPLOCK® PA6 / PA12
 Demand of increased liquid tightness
 For indoor and outdoor use

Product features

All around locking mechanism due to 360° tooth system
 Locking mechanism with integrated coding system
 Extended sealing range across multiple corrugated conduit waves

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Certifications:	IEC EN 61386-23 EN 45545-2 HL3
Colour delivered:	Grey (RAL 7005) Black (RAL 9005), UV-resistant
Material:	PA 6 Halogen-free Fire behaviour according to UL 94V-0
Protection rating:	IP66/IP67/IP68/IP69
Temperature range:	-45°C to +120°C

Last Update (17.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FIPLOCK® ONE ST-PG

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

FIPLOCK® ONE ST-PG

Article number	PG size	Clamping range in mm	SW 1/2 mm	Thread length mm	Suitable for FIPLOCK® PA6 / PA12	Colour	Pieces / PU
FIPLOCK® ONE ST-PG black							
61804836	9	3.5 - 8.0	19.0 / 20.0	8	10	black	10
61804837	9	3.5 - 8.0	19.0 / 22.0	8	12	black	10
61804838	11	4.0 - 10.0	22.0 / 22.0	8	12	black	10
61804839	13.5	6.0 - 12.0	24.0 / 22.0	9	12	black	10
61804841	13.5	6.0 - 12.0	24.0 / 27.0	9	17	black	10
61804842	16	9.0 - 14.0	27.0 / 27.0	10	17	black	10
61804843	16	9.0 - 14.0	27.0 / 36.0	10	23	black	6
61804844	21	13.0 - 18.0	33.0 / 36.0	11	23	black	6
61804845	29	14.0 - 25.0	42.0 / 41.0	11	29	black	6
61804846	36	24.0 - 32.0	53.0 / 52.0	13	36	black	4
61804847	48	39.0 - 44.0	65.0 / 65.0	14	48	black	4
FIPLOCK® ONE ST-PG grey							
61804848	9	3.5 - 8.0	19.0 / 20.0	8	10	grey	10
61804849	9	3.5 - 8.0	19.0 / 22.0	8	12	grey	10
61804851	11	4.0 - 10.0	22.0 / 22.0	8	12	grey	10
61804852	13.5	6.0 - 12.0	24.0 / 22.0	9	12	grey	10
61804853	13.5	6.0 - 12.0	24.0 / 27.0	9	17	grey	10
61804854	16	9.0 - 14.0	27.0 / 27.0	10	17	grey	10
61804855	16	9.0 - 14.0	27.0 / 36.0	10	23	grey	6
61804856	21	13.0 - 18.0	33.0 / 36.0	11	23	grey	6
61804857	29	14.0 - 25.0	42.0 / 41.0	11	29	grey	6
61804858	36	24.0 - 32.0	53.0 / 52.0	13	36	grey	4
61804859	48	39.0 - 44.0	65.0 / 65.0	14	48	grey	4

Last Update (17.05.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16