

## FIPLOCK® ONE Y-divider

Conduit fitting system for highest requirements, suitable for FIPLOCK® PA6 / PA12

FIPLOCK® ONE Y-divider

### Info

New conduit fitting system with innovative locking system



Rail



Good chemical resistance



Flame-retardant



Halogen-free



Cold-resistant



Maximum vibration protection



Mechanical resistance



Assembly time



Low weight

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## FIPLOCK® ONE Y-divider



Optimum strain relief



Robust



Reliability



UV-resistant



Waterproof



### Benefits

Very high tensile strength due to all around tooth system  
 Ensures mounting safety due to integrated coding system  
 Excellent IP rating  
 Cost-saving due to quick and easy installation

### Application range

Suitable for FIPLOCK® PA6 / PA12  
 Demand of increased liquid tightness  
 For indoor and outdoor use

### Product features

All around locking mechanism due to 360° tooth system  
 Locking mechanism with integrated coding system  
 Extended sealing range across multiple corrugated conduit waves

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Certifications:	IEC EN 61386-23 EN 45545-2 HL3
Colour delivered:	Grey (RAL 7005) Black (RAL 9005), UV-resistant
Material:	PA 6 Halogen-free Fire behaviour according to UL 94V-0
Protection rating:	IP66/IP67/IP68/IP69
Temperature range:	-45°C to +120°C

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## FIPLOCK® ONE Y-divider

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**FIPLOCK® ONE Y-divider**

Article number	Nominal size	Hole Ø (mm)	Suitable for FIPLOCK® PA6 / PA12	Colour	Pieces / PU
FIPLOCK® ONE-Y black					
61804977	10-07-07	M4	7 / 10	black	10
61804978	12-10-10	M4	10 / 12	black	10
61804979	17-12-12	M5	12 / 17	black	10
61804980	23-17-17	M6	17 / 23	black	6
61804981	29-23-23	M6	23 / 29	black	6
61804982	36-29-29	M6	29 / 36	black	4
61804983	48-36-36	M6	36 / 48	black	4
FIPLOCK® ONE-Y grey					
61804984	10-07-07	M4	7 / 10	grey	10
61804985	12-10-10	M4	10 / 12	grey	10
61804986	17-12-12	M5	12 / 17	grey	10
61804987	23-17-17	M6	17 / 23	grey	6
61804988	29-23-23	M6	23 / 29	grey	6
61804989	36-29-29	M6	29 / 36	grey	4
61804991	48-36-36	M6	36 / 48	grey	4

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

 You can find the current technical data in the corresponding data sheet.  
 PN 0456 / 02\_03\_16

## FIPLOCK® ONE Y-divider

