

SILVYN® KLICK-GPZ

SILVYN® KLICK-GPZ - PG conduit fitting with integrated cable strain relief for SILVYN® RILL



Wide clamping range



Assembly time



Optimum strain relief



Temperature-resistant



Variety of approval certifications

Benefits

- Fast assembly
- Easy to disassemble
- Additional cable strain relief
- Additional cable sealing

Application range

In combination with protective conduit:

SILVYN® RILL PA 6

SILVYN® RILL PA 12

Robot-building

Used in areas where cables and wires need to be provided with strain relief and additional sealing

Norm references / Approvals

UL FILENUMBER E308201

SILVYN® KLICK-GPZ

Product Make-up

PG connection thread
Cable gland
Body with inner sealing
Upper part with snap-in sleeve

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Colour delivered:	Grey (RAL 7031) Black (RAL 9011), UV-resistant
Material:	PA6
Protection rating:	IP 68 IP 69
Temperature range:	-40 °C to +115 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.



SILVYN® KLICK-GPZ

Article number	PG size	Clamping range in mm	SW wrench size mm	Thread length mm	Clear opening (mm)	For conduit with outer Ø (mm)	Suitable for SILVYN® RILL	Pieces / PU
SILVYN® KLICK-GPZ grey								
61801120	7	3 - 6.5	16	8	7	10	10	20
61801130	9	4 - 8	18	8	8	13	13	20
61801140	11	5 - 10	21	8	10	15.8	16	20
61801200	13.5	6 - 11	21	9	11	15.8	16	20
61801202	13.5	6 - 12	24	9	12	18.5	18	20
61801150	16	10 - 14	27	10	14	21.2	21	10
61801160	21	13 - 18	34	11	20	28.5	28	10
61801170	29	18 - 25	40	11	25	34.5	34	10
61801180	36	22 - 32	55	13	32	42.5	42	10
61801190	48	34 - 44	65	14	44	54.5	54	10
SILVYN® KLICK-GPZ black								
61801125	7	3 - 6.5	16	8	7	10	10	20
61801135	9	4 - 8	18	8	8	13	13	20
61801145	11	5 - 10	21	8	10	15.8	16	20
61801205	13.5	6 - 11	21	9	11	15.8	16	20
61801215	13.5	6.0 - 12.0	24	9	12	18.5	18	20
61801155	16	10 - 14	27	10	14	21.2	21	10
61801165	21	13 - 18	34	11	20	28.5	28	10
61801175	29	18 - 25	40	11	25	34.5	34	10
61801185	36	22 - 32	55	13	32	42.5	42	10
61801195	48	34 - 44	65	14	44	54.5	54	10

Last Update (23.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16