

## SILVYN® KCLICK-RH

SILVYN® KCLICK-RH - conduit holder for SILVYN® RILL

### Info

One-piece conduit holder



Assembly time



Temperature-resistant

### Benefits

- Fast assembly
- Easy to disassemble
- High tensile strength
- Conduit retained by rib
- No loose parts

### Application range

- In combination with protective conduit
- SILVYN® RILL PA 6
- SILVYN® RILL PA 12
- Fastening of conduits on machine walls for all applications

### Product features

- Impact-resistant polyamide
- One-piece conduit holder
- Suitable for mounting onto a C-profile rail
- Stackable

### Product Make-up

One-piece conduit holder with M5/M6 borehole for fixation

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001171

ETIM 5.0 Class-Description: Holder for protective hose

Last Update (23.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® KCLICK-RH

|                        |                                                                                       |
|------------------------|---------------------------------------------------------------------------------------|
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC001171<br>ETIM 6.0 Class-Description: Holder for protective hose |
| Colour delivered:      | Grey (RAL 7031)<br>Black (RAL 9011), UV-resistant                                     |
| Material:              | PA6<br>Halogen-free                                                                   |
| Temperature range:     | -40 °C to +115 °C                                                                     |

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

# SILVYN® KLICK-RH

| Article number         | Nominal size | Hole Ø (mm) | Suitable for SILVYN® RILL | Pieces / PU |
|------------------------|--------------|-------------|---------------------------|-------------|
| SILVYN® KLICK-RH grey  |              |             |                           |             |
| 65500630               | 10           | 5           | 10                        | 50          |
| 65500631               | 13           | 5           | 13                        | 50          |
| 65500632               | 16           | 6           | 16                        | 50          |
| 65500633               | 18           | 6           | 18                        | 50          |
| 65500634               | 21           | 6           | 21                        | 50          |
| 65500635               | 28           | 6           | 28                        | 25          |
| 65500636               | 34           | 6           | 34                        | 25          |
| 65500637               | 42           | 6           | 42                        | 25          |
| 65500638               | 54           | 6           | 54                        | 10          |
| SILVYN® KLICK-RH black |              |             |                           |             |
| 65500639               | 10           | 5           | 10                        | 50          |
| 65500640               | 13           | 5           | 13                        | 50          |
| 65500641               | 16           | 6           | 16                        | 50          |
| 65500642               | 18           | 6           | 18                        | 50          |
| 65500643               | 21           | 6           | 21                        | 50          |
| 65500644               | 28           | 6           | 28                        | 25          |
| 65500645               | 34           | 6           | 34                        | 25          |
| 65500646               | 42           | 6           | 42                        | 25          |
| 65500647               | 54           | 6           | 54                        | 10          |