

SILVYN® KCLICK-Y (TPE)

SILVYN® KCLICK-Y (TPE) - divider in Y-shape for SILVYN® RILL



Assembly time



Temperature-resistant

Benefits

Easy to assemble
High temperature resistance

Application range

In combination with protective conduit:
SILVYN® RILL PA 6
SILVYN® RILL PA 12
Y-distributor for SILVYN® RILL conduits

Product Make-up

3 x conduit connection
1 x bore hole for fixation with M4 screws

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001172

ETIM 5.0 Class-Description: Coupler for corrugated plastic hoses

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001172

ETIM 6.0 Class-Description: Coupler for corrugated plastic hoses

Colour delivered:

Grey (RAL 7031)

Black (RAL 9011), UV-resistant

Material:

TPE

Protection rating:

IP 66

Temperature range:

-40 °C to +115 °C

Note

Last Update (22.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® KCLICK-Y (TPE)

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® KLICK-Y (TPE)

Article number	Nominal size	For conduit with outer Ø (mm)	Suitable for SILVYN® RILL	Pieces / PU
SILVYN® KLICK-Y (TPE) grey				
56000120	3 x 10	10	10	10
56000140	2 x 16/1 x 21	15.8 / 21.2	16/21	10
56000150	2 x 21/1 x 28	21.2 / 28.5	21/28	10
56000160	2 x 28/1 x 34	28.5 / 34.5	28/34	10
SILVYN® KLICK-Y (TPE) black				
56000125	3 x 10	10	10	10
56000145	2 x 16/1 x 21	15.8 / 21.2	16/21	10
56000155	2 x 21/1 x 28	21.2 / 28.5	21/28	10
56000165	2 x 28/1 x 34	28.5 / 34.5	28/34	10

Last Update (22.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16