

SILVYN® KLICK-Y

SILVYN® KLICK-Y - divider in Y-shape for SILVYN® RILL



Assembly time



Temperature-resistant

Benefits

- Fast assembly
- Easy to disassemble
- High-tensile
- Easy combination of different conduit sizes

Application range

In combination with protective conduit
SILVYN® RILL PA 6
SILVYN® RILL PA 12
Y-distributor for SILVYN® RILL conduits

Norm references / Approvals

UL FILENUMBER E308201

Product Make-up

3 x conduit connection
2 x bore hole for fixation with M5 screws

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001172

ETIM 5.0 Class-Description: Coupler for corrugated plastic hoses

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001172

ETIM 6.0 Class-Description: Coupler for corrugated plastic hoses

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® KCLICK-Y

On request:	More sizes / combinations
Colour delivered:	Grey (RAL 7031) Black (RAL 9011), UV-resistant
Material:	PA6 Halogen-free
Protection rating:	IP 68 IP 69
Temperature range:	-40 °C to +115 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® KLICK-Y

Article number	Nominal size	For conduit with outer Ø (mm)	Suitable for SILVYN® RILL	Pieces / PU
SILVYN® KLICK-Y grey				
61801090	2 x 10/1 x 13	10 / 13	10/13	10
61801100	3 x 13	13	13	10
61801110	2 x 13/1 x 16	13 / 15.8	13/16	10
56000130	3 x 16	15.8	16	10
SILVYN® KLICK-Y black				
61801095	2 x 10/1 x 13	10 / 13	10/13	10
61801105	3 x 13	13	13	10
61801115	2 x 13/1 x 16	13 / 15.8	13/16	10
56000135	3 x 16	15.8	16	10

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16