


SILVYN® SHRINK BRAID PET

SILVYN® SHRINK BRAID PA6 - shrinkable braided sleeving

Info

Shrinkable abrasion protection



Wide clamping range



Low weight



Reliability



Temperature-resistant



UV-resistant

Benefits

Additional abrasion protection for critical areas
Cut into length without frizzle on the conduit's end
Simple, fast cable bundling
Protection against dust

Application range

Easy cable protection
Additional insulation
Bundling and guiding of cables and wires
Low rodent-protection

Product features

Abrasion-resistant
Flexible
Shrinkable
Shrinking ratio: 2:1
Maximum length lost after shrinkage is less than 15 %

Last Update (21.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® SHRINK BRAID PET

Product Make-up

Polyester - PET with shrinkable Polyolefin fibres

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001182

ETIM 5.0 Class-Description: Braided hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001182

ETIM 6.0 Class-Description: Braided hose

On request:

Bulk containers on rolls

More sizes available

Note:

No dielectric strength

Self extinguishing acc. to UL94 HB

Colour delivered:

Black (RAL 9005), UV-resistant

Material:

Polyester - PET with shrinkable Polyolefin fibres

Temperature range:

-40 °C to +150 °C

Processing: min. +180 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® SHRINK BRAID PET

Article number	Nominal size	Shrinkage range mm	Colour	PU (m)
SILVYN® SHRINK BRAID PET				
61721270	12/06	12 - 6	black	5
61721271	25/12	25 - 12	black	5
61721272	30/15	30 - 15	black	5
61721273	50/25	50 - 25	black	4
61721274	70/35	70 - 35	black	4