

SILVYN® MPC 90° M

SILVYN® MPC 90° M - conduit fitting for use with SILVYN® EL/ELU/ELO/ELT



Halogen-free



Mechanical resistance



Assembly time



Oil-resistant



Optimum strain relief



Robust



Temperature-resistant



UV-resistant

Benefits

All-purpose

Fast and easy assembly

90° elbow allows easy installation

Application range

In combination with protective conduit:

SILVYN® EL/ELU/ELO/ELT/ELR (helically formed and smooth conduits)

Last Update (15.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® MPC 90° M

Product features

Dust protection
Moisture-protection
Ensures high tensile strength and mechanical protection

Norm references / Approvals

UL FILENUMBER E308201

Product Make-up

Metric connection thread
90° elbow with integrated conduit connection

Note

PG threaded versions are to be found in the online catalogue

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001178 ETIM 5.0 Class-Description: Screw connection for protective plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001178 ETIM 6.0 Class-Description: Screw connection for protective plastic hose
Certifications:	IEC EN 61386-23
Colour delivered:	Black (RAL 9005), UV-resistant Grey, RAL 7001
Material:	PA66 Halogen-free
Protection rating:	IP 65 with helically formed conduits IP 67 + IP 68 (2bar) with smooth conduits
Temperature range:	-40°C to +120°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® MPC 90° M**

Article number	Metric size	Clear opening (mm)	Suitable for SILVYN® SI	Suitable for SILVYN® SP/SP-PU	Suitable for SILVYN® EL/ELU/ELO/ELT/ELR	Pieces / PU
SILVYN® MPC 90° M grey						
55502458	16 x 1.5	10.5	13 x 16	12 x 16	16	10
55502459	20 x 1.5/1	10.5	13 x 16	12 x 16	16	10
55502366	20 x 1.5/2	14.5	-	16 x 20	20	10
55502367	25 x 1.5	19	-	22 x 27	25	10
55502368	32 x 1.5	24.5	-	-	32	10
55502369	40 x 1.5	33	-	-	40	2
SILVYN® MPC 90° M black						
55502480	16 x 1.5	10.5	13 x 16	12 x 16	16	10
55502481	20 x 1.5/1	10.5	13 x 16	12 x 16	16	10
55502482	20 x 1.5/2	14.5	-	16 x 20	20	10
55502483	25 x 1.5	19	-	22 x 27	25	10
55502484	32 x 1.5	24.5	-	-	32	10
55502485	40 x 1.5	33	-	-	40	2

Last Update (15.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16