

## SILVYN® MPC-M

SILVYN® MPC-M - conduit fitting for use with SILVYN® EL/ELU/ELO/ELT



Halogen-free



Mechanical resistance



Assembly time



Oil-resistant



Optimum strain relief



Robust



Temperature-resistant



UV-resistant

### Benefits

All-purpose

Fast and easy assembly

### Application range

In combination with protective conduit:

SILVYN® EL/ELU/ELO/ELT/ELR (helically formed and smooth conduits)

## SILVYN® MPC-M

### Product features

Dust protection  
Moisture-protection  
Ensures high tensile strength and mechanical protection

### Norm references / Approvals

UL FILENUMBER E308201

### Product Make-up

Metric connection thread  
Hexagonal collar with integrated conduit connection

### Note

PG threaded versions are to be found in the online catalogue

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001178 ETIM 5.0 Class-Description: Screw connection for protective plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001178 ETIM 6.0 Class-Description: Screw connection for protective plastic hose
Certifications:	IEC EN 61386-23
Colour delivered:	Black (RAL 9005), UV-resistant Grey, RAL 7001
Material:	PA66 Halogen-free
Protection rating:	IP 65 with helically formed conduits IP 67 + IP 68 (2bar) with smooth conduits
Temperature range:	-40°C to +120°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® MPC-M**

Article number	Metric size	Clear opening (mm)	Suitable for SILVYN® SI	Suitable for SILVYN® SP/SP-PU	Suitable for SILVYN® EL/ELU/ELO/ELT/ELR	Pieces / PU
<b>SILVYN® MPC-M grey</b>						
55502441	16 x 1.5/1	9	11 x 14	-	12	10
55502442	16 x 1.5/2	10.5	13 x 16	12 x 16	16	10
55502443	20 x 1.5/1	10.5	13 x 16	12 x 16	16	10
55502444	20 x 1.5/2	14.5	-	16 x 20	20	10
55502445	25 x 1.5	19	-	22 x 27	25	10
55502446	32 x 1.5/1	24.5	-	-	30	10
55502447	32 x 1.5/2	24.5	-	-	32	10
55502448	40 x 1.5	33	-	-	40	2
55502449	50 x 1.5	39	-	-	50	2
55502439	63 x 1.5	48	-	49 x 56	63	1
<b>SILVYN® MPC-M black</b>						
55502460	16 x 1.5/1	9	11 x 14	-	12	10
55502461	16 x 1.5/2	10.5	13 x 16	12 x 16	16	10
55502462	20 x 1.5/1	10.5	13 x 16	12 x 16	16	10
55502463	20 x 1.5/2	14.5	-	16 x 20	20	10
55502464	25 x 1.5	19	-	22 x 27	25	10
55502465	32 x 1.5/1	24.5	-	-	30	10
55502469	32 x 1.5/2	24.5	-	-	32	10
55502466	40 x 1.5	33	-	-	40	2
55502467	50 x 1.5	39	-	-	50	2
55502468	63 x 1.5	48	-	49 x 56	63	1

Last Update (16.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16