

KW plastic coil

Plastic coils are used for easy and quick bundling of cables and conductors.



Good chemical resistance



Flame-retardant



Mechanical resistance



UV-resistant

Benefits

Flexibility of the cables is largely preserved

Spiral-shaped cut tube

For time-saving cable and wire bundling

Application range

For the manufacturing of cable harnesses with branch-offs

For protection against mechanical stress

Product features

Black version: Fire behaviour according to UL 94 HB

Included

Article no. 61759940: Winding tool

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002604

ETIM 5.0 Class-Description: Cable bundle hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002604

ETIM 6.0 Class-Description: Cable bundle hose

General:

Black version: UV-resistant

Material:

Black version: polyamide (silikone free and halogene free)

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

KW plastic coil

Temperature range:

Nature and coloured version: polyethylene

Black version: -40°C to +120°C

Natural and coloured Version:
-50°C to 85°C

Note

Other sizes and colours are available upon request.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

KW plastic coil

Article number	Article description	Colour	Bundling area (mm)	PU (m)
KW plastic coil				
61600010	Plastic spiral KW 2	natural	2.0 - 7.0	50
61600015	Plastic spiral KW 2	black	2.0 - 7.0	50
61722850	Plastic spiral KW 2	blue	2.0 - 7.0	50
61722856	Plastic spiral KW 2	yellow	2.0 - 7.0	50
61600040	Plastic spiral KW 5	natural	5.0 - 20.0	30
61600045	Plastic spiral KW 5	black	5.0 - 20.0	25
61722851	Plastic spiral KW 5	blue	5.0 - 20.0	25
61600050	Plastic spiral KW 5	yellow	5.0 - 20.0	25
61600070	Plastic spiral KW 10	natural	10.0 - 40.0	30
61722840	Plastic spiral KW 10	black	10.0 - 40.0	25
61722852	Plastic spiral KW 10	blue	10.0 - 40.0	25
61600080	Plastic spiral KW 10	yellow	10.0 - 40.0	25