

Cable trolley system for C-rails

Lapp Group offers a complete cable trolley system both for flat cables and for round cables.

Info

Configuration tool on our homepage (Knowledge center-cable accessories)



Benefits

Gentle cable clamps prevent the cables from sharp bends
Dustproof ball bearing (wheels) guarantee smooth running in the rails

Application range

Crane and conveying machinery
For hoisting equipment and conveyor systems
Mechanical engineering
Washing plants
Not suitable for applications in explosive environments

Note

Round- and flat cables are not allowed to be combined side by side or below each other
Don't assemble more than three clamps for round cables below each other
Bending radius on the bracket corresponds to a fixed installation
Cable trolleys with suffix "b" are suitable for cables with a larger bending radius (see data sheet)

Included

Delivery length of the C-profile 6 m

Product Make-up

The installation of a system depends on various criteria, e.g. maximum cable slack (cable weight) and working length.

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002935

ETIM 5.0 Class-Description: Accessories for cable carrying system

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002935

ETIM 6.0 Class-Description: Accessories for cable carrying system

General:

Max. cable load:

Last Update (21.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

Cable trolley system for C-rails

	C30 System: 20 kg
	C40 System: 32 kg
Material:	Metal parts: Galvanized steel
	Clamps: Polyamide 6
Temperature range:	-40 °C to +120 °C

Note

CIBES® is a registered trade mark of INOMEK AB

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Cable trolley system for C-rails

Article number	Article designation	System	Max. flat cable dimensions mm	max. round cable diameter mm	Pieces / PU
Cable trolley flat cables					
62200421	Cable trolley flat C30 15x54	C30	15.0 x 54.0	-	1
62200442	Cable trolley flat C30 30x54	C30	30.0 x 54.0	-	1
62200477	Cable trolley flat C30 22x54 b	C30	22.0 x 54.0	-	1
62200420	Towing trolley flat C30 30x54	C30	30.0 x 54.0	-	1
62200482	Towing trolley flat C30 22x54 b	C30	22.0 x 54.0	-	1
62200422	End clamp flat C30 30x54	C30	30.0 x 54.0	-	1
62200483	End clamp flat C30 22x54 b	C30	22.0 x 54.0	-	1
62200464	Cable trolley flat C40 22x52	C40	22.0 x 52.0	-	1
62200479	Cable trolley flat C40 22x72	C40	22.0 x 72.0	-	1
62200419	Cable trolley flat C40 22x97	C40	22.0 x 97.0	-	1
62200480	Cable trolley flat C40 22x132	C40	22.0 x 132.0	-	1
62200446	Cable trolley flat C40 35x72	C40	35.0 x 72.0	-	1
62200457	Cable trolley flat C40 35x97	C40	35.0 x 97.0	-	1
62204505	Cable trolley flat C40 35x132	C40	35.0 x 132.0	-	1
62200465	Towing trolley flat C40 22x52	C40	22.0 x 52.0	-	1
62200488	Towing trolley flat C40 22x72	C40	22.0 x 72.0	-	1
62200418	Towing trolley flat C40 22x97	C40	22.0 x 97.0	-	1
62200489	Towing trolley flat C40 22x132	C40	22.0 x 132.0	-	1
62200447	Towing trolley flat C40 35x72	C40	35.0 x 72.0	-	1
62200458	Towing trolley flat C40 35x97	C40	35.0 x 97.0	-	-
62200466	Towing trolley flat C40 35x132	C40	35.0 x 132.0	-	1
62200484	End clamp flat C40 22x52	C40	22.0 x 52.0	-	1
62200485	End clamp flat C40 22x72	C40	22.0 x 72.0	-	1
62200417	End clamp flat C40 22x97	C40	22.0 x 97.0	-	1
62200486	End clamp flat C40 22x132	C40	22.0 x 132.0	-	1
62200448	End clamp flat C40 35x72	C40	35.0 x 72.0	-	1
62200459	End clamp flat C40 35x97	C40	35.0 x 97.0	-	1
62204504	End clamp flat C40 35x132	C40	35.0 x 132.0	-	1
Cable trolley round cable					
62200434	Cable trolley round C30	C30	-	-	1
62200435	Towing trolley round C30	C30	-	-	1

Last Update (21.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

Cable trolley system for C-rails

Article number	Article designation	System	Max. flat cable dimensions mm	max. round cable diameter mm	Pieces / PU
62200478	Cable trolley round C40	C40	-	-	1
62200481	Towing trolley round C40	C40	-	-	1
62200437	Clamp round 10-16mm	-	-	10.0 - 16.0	1
62200438	Clamp round 17-25mm	-	-	17.0 - 25.0	1
62200439	Clamp round 26-36mm	-	-	26.0 - 36.0	1
62200436	End clamp round	C30, C40	-	-	1
Fastening components					
62200440	C Profile rail 6m C30	C30	-	-	1
62200424	Track coupler C30	C30	-	-	1
62200427	Support brackets flex. C30	C30	-	-	1
62200429	Support brackets wall C30	C30	-	-	1
62200425	End stop C30	C30	-	-	1
62200432	Support arm 800mm C30	C30	-	-	1
62200444	C Profile rail 6m C40	C40	-	-	1
62200445	Track coupler C40	C40	-	-	1
62200456	Support brackets flex. C40	C40	-	-	1
62200461	Support brackets wall C40	C40	-	-	1
62200449	End stop C40	C40	-	-	1
62200467	Support arm 800mm C40	C40	-	-	1
62200460	Wall bracket	C30, C40	-	-	1
62200430	Towing arm 400mm	C30, C40	-	-	1
62200431	Towing arm 630mm	C30, C40	-	-	1
62200433	Girder clips	C30, C40	-	-	1
62200471	-	-	-	-	1
62200428	Rail bracket for ceiling mounting	-	-	-	1