

Deciband AHIB

insulated conductor end sleeves with mini-crimp seal, small packaging unit



Halogen-free

Application range

Packs of insulated conductor end sleeves with mini-crimp seal

Included

Insulated conductor end sleeves in standard length in strips with 10 linked mini-crimp bags of 100 conductor end sleeves
Mini crimp lock for individual separation of bags

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000005

ETIM 5.0 Class-Description: Cable end sleeve

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000005

ETIM 6.0 Class-Description: Cable end sleeve

General:

Halogen-free

Material:

Copper/PP

Surface: tin-plated

Temperature range:

-5 °C to +105 °C

Note

Other sizes and colours are available upon request.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Deciband AHIB

Article number	Article designation	For mm ²	Colour	l1 mm	l2 mm	d1 mm	s1 mm	d2 mm	s2 mm	Content	Pieces / PU
61794760	Deciband AHIB	0.34	turquoise	10.5	6	0.8	0.25	2	0.25	10 x 100	1
61794770	Deciband AHIB	0.5	orange	13.5	8	1.1	0.15	2.5	0.25	10 x 100	1
61794780	Deciband AHIB	0.75	white	14	8	1.3	0.15	2.8	0.25	10 x 100	1
61794790	Deciband AHIB	1	yellow	14.5	8	1.5	0.15	3	0.3	10 x 100	1
61794800	Deciband AHIB	1.5	red	14.5	8	1.8	0.15	3.4	0.3	10 x 100	1
61794810	Deciband AHIB	2.5	blue	15	8	2.3	0.15	4.2	0.3	10 x 100	1

Last Update (25.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16