

DKB 0325 + DKB 0360 crimping pliers

DKB 0325/DKB 0360: Crimping pliers for pressing non-insulated cable lugs from 0,35-6,0 mm², Crimping profile: mandrel pressing, ergonomic design



Reliability

Benefits

- Locking function for faultless pressing
- Clearly marked press moulds
- Less force required for perfect pressing
- Tested for a minimum of 80,000 pressings

Application range

Safety pressing pliers for non-insulated connections
For non-insulated cable lugs, other connectors and tubular cable lugs KR

Product features

Emergency release, if the pressing operation needs to be interrupted

Norm references / Approvals

Tested in accordance with DIN standard EN 60352-2

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000168

ETIM 5.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000168

ETIM 6.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

General:

Adjustable crimping pressure

Note:

Crimping profile: Mandrel pressing

Note

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

DKB 0325 + DKB 0360 crimping pliers

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

DKB 0325 + DKB 0360 crimping pliers

Article number	Article designation	For mm²	Crimping profile	Weight (kg)	Length (mm)	Pieces / PU
61722110	DKB 0325	0.35 - 2.5	mandrel pressing	0.35	192	1
61790920	DKB 0360	0.35 - 6	mandrel pressing	0.35	192	1