

KRB 0560 crimping pliers

KRB 0560: Crimping pliers for pressing for non-insulated blade connectors/panel connectors 4,8 and 6,3 from 0,5-6mm², Crimping profile: roller pressing, ergonomic design



Reliability

Benefits

- Clearly marked press moulds
- Locking function for faultless pressing
- Handles suit both large and small hands
- Unique mechanism reduces the manual force from 450 N to 250 N
- Tested for a minimum of 80,000 pressings

Application range

The convenient roll pressing pliers for non-insulated blade connectors of 0.5 - 6 mm² with connection 4.8 and 6.3

Product features

Emergency release, if the pressing operation needs to be interrupted

Norm references / Approvals

Tested in accordance with DIN standard EN 60352-2

Note

The locator ensures the right positioning of the insulation and wire crimp which is particular important for the crimp quality of blade connectors.

Included

Article number 61790950 is delivered without locator

Article number 61791100 contains locator

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000168

ETIM 5.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000168

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

KRB 0560 crimping pliers

General:

ETIM 6.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

Adjustable crimping pressure

Note:

Crimping profile: Roller pressing

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

KRB 0560 crimping pliers

Article number	Article designation	For mm ²	Crimping profile	For blade connectors	Weight (kg)	Length (mm)	Pieces / PU
61790950	KRB 0560 without locator	0.5 - 6	roller pressing	4.8 + 6.3	0.54	255	1
61791100	KRB 0560 with locator	0.5 - 6	roller pressing	4.8 + 6.3	0.54	255	1