

Tube cable lugs KRFS

Tube cable lugs KRFS, also for fine wire copper conductors, class 2, 5 and 6, easy to mount through cable glands



Rail



Suitable for outdoor use



Mechanical resistance



Space requirement

Benefits

Can be installed through cable glands, allowing pre-assembly
 High-quality electrolytic copper ensures a good crimping quality
 With inspection hole
 Same or smaller flange width as pipe diameter

Application range

Tubular cable lugs with particularly narrow flange suitable for stranded, flexible and very flexible CU conductors 50 - 240 mm² (class 2, 5 & 6)
 Adapted for narrow spaces

Norm references / Approvals

UL file number: E205350 (see table)

In combination with recommended crimp tool fulfill requirements of EN-IEC 61238:1, BS 4579:1 and VDE 0220:1

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001051

ETIM 5.0 Class-Description: Tube cable lug for copper

Last Update (26.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

Tube cable lugs KRFS

Material:	conductors Tinned electrolyte copper
Temperature range:	Temperature range up to +90°C Working temperature: 110°C, max. +140°C

Note

* Trade product, no Lapp product

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Tube cable lugs KRFS

Article number	Article designation	Screw hole Ø (mm)	UL certification	Length (mm)	Pressing dies	d mm	W mm	Pieces / PU
61803470	KRFS 50/6	6	no	51	B 14.5	11	15	100
61803471	KRFS 50/8	8	no	51	B 14.5	11	16.5	100
61803472	KRFS 50/10	10	no	52	B 14.5	11	16.5	100
61803473	KRFS 70/6	6	no	58	B 17	13	17	50
61803474	KRFS 70/8	8	no	58	B 17	13	17	50
61803475	KRFS 70/10	10	no	58	B 17	13	19	50
61803476	KRFS 95/6	6	yes	63	B 20	15	19	50
61803477	KRFS 95/8	8	yes	63	B 20	15	19	50
61803478	KRFS 95/10	10	yes	63	B 20	15	19	50
61803479	KRFS 95/12	12	yes	64	B 20	15	20	50
61803480	KRFS 120/6	6	yes	67	B 22	17	19	25
61803481	KRFS 120/8	8	yes	67	B 22	17	19	25
61803482	KRFS 120/10	10	yes	67	B 22	17	19	25
61803483	KRFS 120/12	12	yes	70	B 22	17	22	25
61803484	KRFS 150/6	6	yes	74	B 25/13 B 25	19	25	25
61803485	KRFS 150/8	8	yes	74	B 25/13 B 25	19	25	25
61803486	KRFS 150/10	10	yes	74	B 25/13 B 25	19	25	25
61803487	KRFS 150/12	12	yes	76	B 25/13 B 25	19	25	25
61803488	KRFS 185/10	10	yes	79	13 B 27	21	27	20
61803489	KRFS 185/12	12	yes	82	13 B 27	21	27	20
61803490	KRFS 240A/10	10	yes	91	13 B 30	22.5	29	10
61803491	KRFS 240A/12	12	yes	91	13 B 30	22.5	29	10
61803492	KRFS 240A/16	16	yes	96	13 B 30	22.5	29	10

Last Update (26.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

Tube cable lugs KRFS

