

KNIPEX Alligator® Water pump plier

KNIPEX Insulated pliers for gripping and cutting work

Info

Good access to the workpiece due to slim size



Benefits

Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
High ergonomics thanks to multi-component handles
Insulated handles allow working under voltage up to 1000V

Application range

Insensitive to dirt due to robust construction, hence particularly suitable for outdoor work

Product features

9-notch adjustment positioning
High wear resistance of the gripping surfaces

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000164 ETIM 5.0 Class-Description: Water pump plier
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000164 ETIM 6.0 Class-Description: Water pump pliers
Certifications:	Insulated according to IEC 60900, applicable up to 1000V AC / 1500V DC VDE-tested
Material:	Chrome vanadium electric steel, forged, multi stage oil- hardened

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

KNIPEX Alligator® Water pump plier

Article number	Article designation	Clamping width mm	Jaw distance mm	Weight (kg)	Length (mm)
62120505	Water pump plier WPZI 25	50	46	0.374	250

Last Update (14.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16