

KNIPEX High leverage combination plier

KNIPEX Insulated pliers for gripping and cutting work

Info

35 % less effort required than with conventional combination pliers



Benefits

High ergonomics thanks to multi-component handles
Insulated handles allow working under voltage up to 1000V

Application range

With gripping zones for versatile use
With cutting edges for heavy duty and thicker cables

Product features

Long cutting edges for thicker cables

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000836 ETIM 5.0 Class-Description: Combination pliers
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000836 ETIM 6.0 Class-Description: Combination pliers
Certifications:	Insulated according to IEC 60900, applicable up to 1000V AC / 1500V DC VDE-tested
Material:	High-grade special tool steel, forged, multi stage oil-hardened

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

KNIPEX High leverage combination plier

Article number	Article designation	Hard wire mm	Pianowire mm	Cable diameter mm	Weight (kg)	Length (mm)
62120504	High leverage combination plier KKZI 20	2.8	2.2	13	0.343	200