

KNIPEX Snipe nose side cutting pliers

KNIPEX Insulated pliers for gripping and cutting work

Info

With cutting edges



Benefits

High ergonomics thanks to multi-component handles
Insulated handles allow working under voltage up to 1000V

Application range

Suitable for finer gripping work

Product features

Pointed, half-rounded jaws, knurled gripping surfaces, with cutting edges

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000833 ETIM 5.0 Class-Description: Combination pliers
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000833 ETIM 6.0 Class-Description: Flat nose pliers
Certifications:	Insulated according to IEC 60900, applicable up to 1000V AC / 1500V DC VDE-tested
Material:	Vanadium electric steel, forged, oil-hardened

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

KNIPEX Snipe nose side cutting pliers

Article number	Article designation	Medium hard wire mm	Hard wire mm	Weight (kg)	Length (mm)
Snipe nose side cutting plier					
62120503	Snipe nose plier FRZI 16	2.5	1.6	0.144	160