


21700623	DATA SHEET	
Valid from: 17.09.2018	EPIC DATA CCR FA	

Product description

- Field mountable cable coupler class F_A for 8 wire cables
- to repair / extend / relocate data cables up to Cat. 7_A
- suitable for industrial applications
- Robust and consistent against vibration
- No special tools needed



General properties

Ambient temperature	-40 to +85 °C
Protection degree	IP 67
Termination type	IDC
Outer diameter, cable	5.0 – 9.7 mm
Outer diameter, wire	0.85 – 1.6 mm
Termination cross section, stranded, 7 wires	AWG26/7 – AWG22/7
Termination cross section, solid	AWG26/1 – AWG22/1
Pollution degree	1

Electrical properties

Rated voltage	48 V
Current carrying capacity at 40°C	0.5 A
Insulating resistance	≥ 100 MΩ

Transmission properties

Suitable for 10 Gigabit Ethernet acc. to IEEE 802.3an	yes
Class F _A	ISO/IEC 11801


Materials

Connector housing, base material	die-cast zinc
Connector housing, surface	Ni
Contacts, surface	Sn


Approvals

UL listed, E-File	E353543
-------------------	---------

Creator: MANA2/PDP Released: IVSE1/PDP	Document: DB21700623EN Version: 02	Page 1 of 2
---	---------------------------------------	-------------

21700623	DATA SHEET	
Valid from: 17.09.2018	EPIC DATA CCR FA	

Drawings



Application range

Automation, industrial machinery and plant engineering

Note

Photographs are not true to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP Released: IVSE1/PDP	Document: DB21700623EN Version: 02	Page 2 of 2
---	---------------------------------------	-------------