EPIC® SENSOR CCR

Cable coupler round, shielded for e.g. sensor-actuator / PROFIBUS / CAN cables

Field mountable round cable coupler, IP67, IDC, for CAN / Profibus / sensor-actuator applications, 360° shielding



Waterproof

Interference signals

Mechanical and plant engineering

Kompletterande automationskomponenter från Lapp

Benefits

Optimum EMC protection with 360 ° shielding
Time-saving assembly with IDC connection technology

Application range

To extend existing cable systems
Repairkit for damaged cables

Product features

5-pin cable coupler round
Screened version

Technical Data

Material:	Contact: CuZn Contact surface: Ni/Au Knurl: Zinc die-cast, nickel-plated Gripping body: Zinc die-cast, nickel-plated
Protection rating:	IP65/IP67

Last Update (22.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® SENSOR CCR

Ambient temperature (operation):	-40 °C to +85 °C
Rated current (A):	4 A

Note

DeviceNet is a registered trademark of ODVA
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (22.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® SENSOR CCR

Article number	Article designation	Number of pins	Cross-section in mm²	Cable diameter in mm	Rated voltage (V)
Cable coupler round					
21700641	AB-C5-CCR-SH	5	18.0 - 26.0	5.0 - 9.7	60

©2024 Lapp Group - Technical changes reserved