

EPIC® H-A 32 SGR

Rugged housings for 2 inserts

The compact, robust metal housing for double size H-A 32 is ideal for machine and device manufacturing and in control systems.

Info
Compact, robust metal housings for double size H-A 32





Waterproof

Robust

Mechanical resistance

Mechanical and plant engineering

Benefits
For two inserts of the small H-A, H-D and STA series. Space-saving

Application range
Machine and equipment manufacturing
Control engineering

Product features
Surface-mount base
Dual levers
1 cable entry

Technical Data
Classification ETIM 5:

ETIM 5.0 Class-ID: EC000437
ETIM 5.0 Class-Description: Housing for industrial connectors

©2023 Lapp Group - Technical changes reserved

EPIC® H-A 32 SGR

Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
VDE-tested:	UL-tested: UL File Number: E75770
Temperature range:	-40°C to +100°C, short-term up to +125°C

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2023 Lapp Group - Technical changes reserved

LAPP

EPIC® H-A 32 SGR

PRODUCT INFORMATION

Article number	Article description	M	PG	Neck
H-A housing: surface-mount base (1 cable entry, double lever)				
10474000	H-A 32 SGR 21	-	21	yes
10474100	H-A 32 SGR 29	-	29	yes
19474000	H-A 32 SGR M25	25	-	yes
19474100	H-A 32 SGR M32	32	-	yes

Last Update (22.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16