
EPIC® H-A 32 TGB

Rugged housings for 2 inserts

The robust housing for 2 inserts of the H-A, H-D or STA series is ideal for space-saving installations. It has 2 double levers and a direct cable entry.

Info
Compact, robust metal housings for double size H-A 32





Mechanical and plant engineering

Mechanical resistance

Robust

Waterproof

Benefits
For two inserts of the small H-A, H-D and STA series. Space-saving
M40 housing extension on M50 with SKINTOP 53112083 possible (clamping range 27 - 35 mm)

Application range
Machine and equipment manufacturing
Control engineering

Product features
Hood
Dual levers
Straight cable entry
Versions with / without neck

Last Update (23.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® H-A 32 TGB

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2024 Lapp Group - Technical changes reserved

LAPP

EPIC® H-A 32 TGB

PRODUCT INFORMATION

Article number	Article description	M	PG	Neck	Pieces / PU
H-A housing: hood (straight cable entry, double lever)					
10585000	H-A 32 TGB 29	-	29	yes	5
19585000	H-A 32 TGB M32	32	-	-	5
79525800	H-A 32 TGB M40	40	-	-	5

Last Update (23.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16